


Feed through and ground terminal blocks

Insulation displacement

ADO - ADO, DIN 3

D 1/5.ADO - 1 mm² blocks - 5 mm .198" spacing



Characteristics		IEC		UL	CSA
		NFC	DIN		
Wire size mm² / AWG	Screw	Solid	—	—	—
		Stranded	—	—	—
ADO		Solid	0.2 - 1 mm²	24-18 AWG	24-18 AWG
		Stranded	0.22 - 1 mm²		
Voltage		V	1000	600	600
Current		A	13.5	7	7
Short circuit current (D 1/5.PI.ADO)		A / s	120 A/1s		
Rated wire size		mm² / AWG	1 mm²	18 AWG	18 AWG



2 wires of the same gauge
and nature
per ADO connection

Selection

Description	Type	Packaging	Catalog Number
Standard block grey	D 1/5.ADO	50	019956324
Standard block orange	D 1/5.ADO	50	019956425
Standard block blue	D 1/5.N.ADO	50	019956526
Standard block black	D 1/5.ADO	50	019956627
Standard block red	D 1/5.ADO	50	019956720
Standard block yellow	D 1/5.ADO	50	019956902
Standard block ivory	D 1/5.ADO	50	019956801
Standard block green	D 1/5.ADO	50	019957007

Accessories

Description	Type	Packaging	Catalog number
End stop	screwless	BADL 9 mm	50
	with screw	BAM2 9.9 mm	50
End section	grey	FEMAD3 3 mm	20
	yellow	FEMAD3 3 mm	20
Assembled jumper bar (with IP20 protection)	2 poles	BJMI5 24 A	10
	3 poles	BJMI5 24 A	10
	4 poles	BJMI5 24 A	10
	5 poles	BJMI5 24 A	10
	10 poles	BJMI5 24 A	10
			10
Shield connector	CBM5	0.5 mm	50
	CBM8	0.8 mm	50



D 1/5.PADO - 1 mm² ground block with rail contact - 5 mm .198" spacing

Characteristics		IEC		UL	CSA
		NFC	DIN		
Wire size mm² / AWG	Screw	Solid	—	—	—
		Stranded	—	—	—
ADO		Solid	0.2 - 1 mm²	24-18 AWG	24-18 AWG
		Stranded	0.22 - 1 mm²		
Short circuit current (D 1/5.PI.ADO)		A / s	120 A/1s	—	—
Rated wire size		mm² / AWG	—	—	—

2 wires of the same gauge
and nature
per ADO connection

Selection

Description	Type	Packaging	Catalog number
Ground block, green body/yellow marking	D 1/5.PADO	50	039903122

Accessories

Description	Type	Packaging	Catalog number
End section	yellow	FEMAD3 3 mm	20
	grey	FEMAD3 3 mm	20

