

Specification Sheet

Part Number: CT1503X2



Self-Laminating Tag, Generic Write-On, Blank Lines, 4.0" x 1.5", Orange, 25/pkg

Article Number	597-00033
Type	CT1503
Color	Orange (OG)
Features & Benefits	• Clear laminating plastic flap permanently protects the writing and data marked on the tag. • Mounting holes for easy mounting using standard cable ties. • Markers can be mounted in any direction, either vertically, horizontally, as a wrap-around identification plate or as a flag for the best visual position on the cable assembly.
Quantity Per	pack

Product Description	HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease. Product Features/bold - Easily and conveniently fits in a pants or shirt pocket. - Once loaded, unit allows minimal label exposure to dust and moisture. - Can be used with standard ball point pens or HellermannTyton nylon marking pens. - Excess liner is easily cut-off by tearing it over the edge guide at the front of the unit. - The dispenser can be reloaded over and over again, making it a cost-effective and efficient method of labeling.
Short Description	Self-Laminating Tag, Generic Write-On, Blank Lines, 4.0" x 1.5", Orange, 25/pkg
Global Part Name	CT1503-PVC-OG
Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	1.5
Height H (Metric)	38.1
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Adhesive	Acrylic
Halogen free	No
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)

Operating Temperature (Metric)

-40°F to +257°F (-40°C to +125°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

25

Package Quantity (Metric)

25

Customs Number

3926909988

Labels per Column

1

Labels per Row

1

Weight (Metric)

0.22

Weight (Imperial)

0.5