

Micro Contactor MA Series



- Relay-sized contactor, making it the world's smallest
- >3mm contact clearance acc. to IEC 60335-1 for Safety Applications
- Reversing contactor with mechanical interlock
- 3 Pole and 1 Aux. Contact NO or NC
- 5A AC3 @ 400VAC (2.2kW) - 12A AC1 @ 400VAC
- AC coil voltages - TS15 DIN rail mounting
- PCB mounting option
- AC and DC coil voltage



Micro Contactor Relays

Page 2



Micro Contactors

Page 3



Micro Contactors With Solder Pins
Coil Voltages

Page 4



Micro Reversing Contactor

Page 5



Technical Data

Page 6

Dimensions

Page 10

Micro Contactor MA Series



IMO

Micro Contactor Relays 4-Pole


AC/DC Operated

Ratings Therm.	Contacts *2	Distinc. Number	Additional Contact	Type	Coil Voltage *1	Pack pcs.	Weight kg/pc.
AC15	Rated-Current				24 24V 50/60Hz 230 220-240V 50/60Hz 24DC 24VDC 42DC 42VDC		
230V A	400V A I_{th} A	NO NC	acc. to EN50011	Blocks Type	↓		
4-Pole, With Screw Terminals							




3	1.5	5	4	-	40E	-	MA04-S-40	...	10	0.07
3	1.5	5	3	1	31E	-	MA04-S-31	...	10	0.07
3	1.5	5	2	2	22E	-	MA04-S-22	...	10	0.07


MA04-S-40



MA04-S-31



MA04-S-22

*1
*2

Other coil voltages - see page 4
 Contacts suitable for electronic circuits, according to EN947-5-4 for rated voltage 24V DC (test ratings 17V DC, 5mA). Positively guided contacts.

Micro Contactor MA Series



Micro Contactors

AC/DC Operated

Power Ratings	Rated Current	Aux. Contacts* ² Built-in	Additional	Type	Coil Voltage * ¹		Pack pcs.	Weight kg/pc.
AC2, AC3	AC1				24 24V 50/60Hz 230 220-240V 50/60Hz 24DC 24VDC 42DC 42VDC			
380V 400V 415V kW	660V 690V kW	440V A	 NO	 NC	Type	↓		

3-Pole, With Screw Terminals


2.2	-	12	1	-	-	MA05-S-10	...	10	0.07
2.2	-	12	-	1	-	MA05-S-01	...	10	0.07

4-Pole, With Screw Terminals


2.2	-	12	-	-	-	MA05-S-0040	...	10	0.07
-----	---	----	---	---	---	-------------	-----	----	------




MA05-S-10



MA05-S-01



MA05-S-0040



Snap-On Adaptor

For Type	Specification	Type	Pack pcs.	Weight kg/pc.
MA	for snap mounting of Snap on Adaptor for MA accessories on 35mm DIN-Rail acc. DIN EN 50022	MA-P1039	10	0.01



*¹ Other coil voltages - see page 4
 *² Contacts suitable for electronic circuits, according to EN947-5-4 for rated voltage 24V DC (test ratings 17V DC, 5mA). Positively guided contacts.

Micro Contactor MA Series



Micro Contactors


AC/DC Operated

Power Ratings		Rated Current	Aux. Contacts*2		Type	Coil Voltage *1		Pack pcs.	Weight kg/pc.
AC2, AC3		AC1	Built-in	Additional					
						24	24V 50/60Hz		
						230	220-240V 50/60Hz		
						24DC	24VDC		
						42DC	42VDC		
						↓			

380V
400V
415V
kW

660V
690V
kW

440V
A



Type

3-Pole, With Solder Pins Ø1.15 For Printed Circuit Applications


2.2	-	9	1	-	-	MA05-P-10	...	10	0.07
2.2	-	9	-	1	-	MA05-P-01	...	10	0.07

4-Pole, With Solder Pins Ø1.15 for Printed Circuit Applications


2.2	-	9	-	-	-	MA05-P-0040	...	10	0.07
-----	---	---	---	---	---	-------------	-----	----	------




MA05-P-10



MA05-P-01



MA05-P-0040



Coil Voltages for AC operated contactors

Suffix to contactor type e.g. MA05-S-1024AC	Voltage Marking at the coil for		Rated Control Voltage U _s range for 50Hz				for 60Hz	
	50Hz	60Hz	min.	max.	min.	max.	min.	max.
	V	V	V	V	V	V	V	V
12	12	12	11	12	12	12		
24	24	24	22	24	24	24		
42	42	42	38.5	42	42	42		
48	48	48	48	50	48	52		
90	100	100	90	100	100	105		
95	95-100	105-110	95	100	105	110		
100	100	110-115	100	105	110	115		
105	105-110	115-120	105	110	115	120		
110	110-115	120-125	110	115	120	125		
180	200	200	185	200	200	210		

*1 Other coil voltages - see above
*2 Contacts suitable for electronic circuits, according to EN947-5-4 for rated voltage 24V DC (test ratings 17V DC, 5mA). Positively guided contacts.

Suffix to contactor type e.g. MA05-S-10230AC	Voltage Marking at the coil for		Rated Control Voltage U _s range for 50Hz				for 60Hz	
	50Hz	60Hz	min.	max.	min.	max.	min.	max.
	V	V	V	V	V	V	V	V
200	200	200-220	195	205	200	220		
210	205-215	220-230	205	215	220	230		
220	210-220	220-240	210	220	220	240		
230	220-230	230-250	220	230	230	250		
240	230-240		230	240	250	260		

Standard voltages in bold type letters
Operating range of magnet-coils: 0.85 x U_s (min value of rated control voltage) up to 1.1 x U_s (max value of rated control voltage)

Coil not exchangeable

Coil Voltages for DC operated contactors

Suffix to contactor type e.g. MA05-S-1012DC	Voltage Marking on the coil	Rated Control Voltage U _s	
		Min.	Max.
12DC	12	10.2	13.2
42DC	42	35.7	46.2

Micro Contactor MA Series




IMO

Micro Reversing Contactors, Mechanical Interlock

AC/DC Operated

Power Ratings	Rated Current	Aux. Contacts* ² Built-in	Additional		Type	Coil Voltage * ¹
			on the left hand side contactor	on right hand side contactor		
AC2, AC3	AC1					24 24V 50/60Hz 230 220-240V 50/60Hz 24DC 24VDC 42DC 42VDC

380V
400V 660V
415V 690V
kW kW
A

K1
TypeK2
TypePack
pcs.Weight
kg/pc.

3-Pole, With Screw Terminals



2.2	-	12	-	1	-	-	MA05-R-S-01	...	1	0.14
2.2	-	12	1	-	-	-	MA05-R-S-10	...	1	0.14

4-Pole, With Screw Terminals


2.2	-	12	-	-	-	-	MA05-R-S-0040	...	1	0.14
-----	---	----	---	---	---	---	---------------	-----	---	------

3-Pole, With Solder Pins Ø1.15 For Printed Circuit Applications




2.2	-	xxx* ³	-	1	-	-	MA05-R-P-01	...	1	0.14
2.2	-	xxx* ³	1	-	-	-	MA05-R-P-10	...	1	0.14


MA05-R-S-01



MA05-R-S-10



MA05-R-S-0040



^{*1} Other coil voltages - see page 4
^{*2} Contacts suitable for electronic circuits, according to EN947-5-4 for rated voltage 24V DC (test ratings 17V DC, 5mA). Positively guided contacts.
^{*3} Data available upon request

Micro Contactor MA Series

Data according to IEC 60947-4-1, VDE 0660, EN 60947-4-1

Main Contacts	Type	MA05-S..
Rated insulation voltage U_i	V AC	480*1
Making capacity I_{eff} at $U_e = 440V$ AC	A	65
Breaking capacity I_{eff} $\cos\varphi = 0.65$ 400V AC	A	50
Utilization category AC1		
Switching of resistive load		
Rated operational current $I_e (=I_{th})$ at 40°C, open	A	12
Rated operational power of three-phase resistive loads 50-60Hz, $\cos\varphi = 1$	230V kW	4.7
	240V kW	4.8
	400V kW	8.3
	415V kW	8.6
	480V kW	9.5
Rated operational current $I_e (=I_{th})$ at 60°C, enclosed	A	8
Rated operational power of three-phase resistive loads 50-60Hz, $\cos\varphi = 1$	230V kW	3.1
	240V kW	3.3
	400V kW	5.5
	415V kW	5.7
	480V kW	6.5
Minimum cross-section of conductor at load with $I_e (=I_{th})$	mm ²	1.5
Utilization category AC2 and AC3		
Switching of three-phase motors		
Rated operational current I_e open and enclosed	220V A	6.2
	230V A	6.2
	240V A	5.6
	380-400V A	5
	415-440V A	5
	480V A	5
Rated operational power of three-phase motors 50-60Hz	220-240V kW	1.5
	380-440V kW	2.2
	480V kW	2.2
Utilization category AC4		
Switching of squirrel cage motors, inching		
Rated operational current I_e open and enclosed	220V A	4.9
	230V A	4.9
	240V A	4.1
	380-400V A	3.5
	415-440V A	3.5
	480V A	3.5
Rated operational power of three-phase motors 50-60Hz	220-240V kW	1.1
	380-440V kW	1.5
	480V kW	1.5

*1 Suitable at 690V for: earthed-neutral systems, overvoltage category I to III, pollution degree 3 (standard-industry): $U_{imp} = 4kV$.
Data for other conditions on request

Micro Contactor MA Series

Data according to IEC 60947-4-1, VDE 0660, EN 60947-4-1

Main Contacts			Type	MA05-S..
Utilization category DC1				
Switching of resistive load		1 pole 24V	A	12
Time constant L/R ≤1ms		60V	A	12
Rated operational current I _o		110V	A	-
		220V	A	-
		3 poles in series 24V	A	12
		60V	A	12
		110V	A	12
		220V	A	-
Utilization category DC3 and DC5				
Switching of shunt motors and series motors		1 pole 24V	A	12
		60V	A	-
Time constant L/R ≤15ms		110V	A	-
Rated operational current I _o		220V	A	-
		3 poles in series 24V	A	12
		60V	A	12
		110V	A	12
		220V	A	-
Maximum ambient temperature				
Operation		open	°C	-40 to +60 (+90)*
		enclosed	°C	-40 to +40
with thermal overload relay		open	°C	-25 to +60
		enclosed	°C	-25 to +40
Storage			°C	-50 to +90
Short circuit protection				
for contactors without thermal overload relay				
Coordination-type “1” according to IEC 947-4-1				
Contact welding without hazard of persons		gL (gG)	A	20
max. fuse size				
Coordination-type “2” according to IEC 947-4-1				
Light contact welding accepted		gL (gG)	A	-
max. fuse size				
Contact welding not accepted				
max. fuse size		gL (gG)	A	-
For contactors with thermal overload relay the device with the smaller admissible backup fuse (contactor or thermal overload relay) determines the fuse size				
Cable cross-sections				
for contactors				
main connector		solid or stranded	mm ²	0.5-1.5
		flexible	mm ²	0.5-1.5
		flexible with multicore cable end	mm ²	0.5-1.5
Cables per clamp				2
		solid or stranded	AWG	20-14
Frequency of operation z				
contactors without thermal overload relay		without load	1/h	10000
		AC3 I _o	1/h	600
		AC4 I _o	1/h	120
		DC3 I _o	1/h	600
Mechanical life		AC operated	S x	10 ⁶
		DC operated	S x	10 ⁶
				xxx* ²
Short time current		10s-current	A	50
Power loss per pole		at I _o /AC3 400V	W	0.2
Resistance to shock according to IEC 68-2-27				
Shick time 20ms sine-wave				
AC operated		NO	g	2.5
		NC	g	2.5

*1 With reduced control voltage range 0.9 up to 1.0 x U_e and with reduced rated current I_o/AC1 according to I_o/AC3

*2 Data on request

Micro Contactor MA Series

Data according to IEC 60947-5-1, VDE 0660, EN 60947-5-1

Auxiliary Contacts		Type	MA04-S.. MA05-S..
Rated insulation voltage	U_i	VAC	440 ^{*1}
Thermal rated current I_{th} bis 440V	40°C	A	5
Ambient temperature	60°C	A	3
Power loss per pole	I_{th}	W	0.25
Utilization category AC15			
Rated operational current I_e	220-240V	A	3
	380-415V	A	1.5
	440V	A	1
Utilization category DC13			
Rated operational current I_e	60V	A	0.5
			-
			-
Maximum ambient temperature			
Operation	open	°C	-40 bis to +60 (+90) ^{*2}
	enclosed	°C	-40 bis to +40
Storage		°C	-40 bis to +90
Short circuit protection			
short circuit current 1kA, contact welding not accepted max fuse size	gL (gG)	A	10
For contactors with thermal overload relay the device with the smaller admissible control fuse (contactor or thermal overload relay) determines the fuse size			
Power consumption of coils			
AC operated	inrush	VA	9
	sealed	VA	4
		W	1.8
Operation range of coils			
in multiples of control voltage U_s			0.85 - 1.1
Switching time at control voltage $U_s \pm 10\%$ ^{*3*4}			
AC operated	make time	ms	13 - 18
	release time	ms	5 - 10
	arc duration	ms	10 - 15
DC operated	make time	ms	-
	release time	ms	-
	arc duration	ms	-
Cable cross-section			
all connectors	solid	mm ²	05 - 1.5
	flexible	mm ²	0.5 - 1.5
	flexible with multicore cable end	mm ²	0.5 - 1.5
Clamps per pole			2
	solid or stranded	AWG	20 - 14

*1 Suitable at 690V for: earthed-neutral systems, overvoltage category I to III, pollution degree 3 (standard-industry): $U_{imp} = 4kV$

Data for other conditions on request

*2 With reduced control voltage range 0.9 up to 1.0 x U_s and with reduced thermal rated current I_{th} to $I_e/AC15$

*3 Summary switching time = release time + arc duration

*4 Release time of NC make time of NO increase when suppressor units for voltage peak protection are used (Varistor, RC-units, Diode units)

*5 Data on request

Micro Contactor MA Series

For North America - Data according UL508

Main Contacts (cULus)	Type	MA05-S.. MA05-R-S..	MA04-S..
Rated operational current "General Use"	A	12	5
Rated operational power of three phase motors at 60Hz (3ph)	110-120V hp	½	-
	200-208V hp	1	-
	220-240V hp	1	-
	277V hp	1½	-
Rated operational power of AC motors at 60Hz (1ph)	110-120V hp	⅙	-
	200-208V hp	½	-
	220-240V hp	¾	-
Fuse / Short circuit current	A/kA	30/5	-
Rated voltage	VAC	300	300
Auxilliary contacts (cULus)	heavy pilot duty AC	B300	B300
	Standard pilot duty DC	R300	R300

Motor Rating $P_n = AC4$




380/ 220/
400V 230V
kW kW

Motor Rating $P_n = AC3$

380/ 220/
400V 230V
kW kW

Breaking Current $I_b (= I_e = AC1)$

A



Millions of Operations



Micro Contactor MA Series

Dimensions

AC Operated
with screw terminals

Snap-On Adaptor MA-P1039



MA04-S..
MA05-S..



Reversing Contactors
with screw terminals

MA..-S.. with Snap-On Adaptor MA-P1039

MA05-R-S..





AC Operated
with solder connections

Reversing Contactors
with solder connections

MA04-P.
MA05-P.

MA05-R-S..



Mounting positions of contactors

MA

