


Multi Input & Multi Output Terminals Push Fit Connection

PFD1.5SD

Width: 4.2 mm



1.5 mm² PushFit Feed Through Terminal Block
1 In, 2 Out
For 35 mm DIN Rail

PFD1.5PE

Width: 4.2 mm



1.5 mm² PushFit Feed Through Terminal Block
1 In, 2 Out, Protective Earth
For 35 mm DIN Rail



Electrical Ratings
CE (EN 60947-7-1 - EN 60947-7-2)
cRUus
VDE (IEC 60947-7-1)
CSA
IECEX

Connection Data
Conductor cross section solid (min.-max.)
Conductor cross section stranded (min.-max.)
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, (min.-max.)
AWG Conductor
Insulation Stripping Length
Screwdriver

Technical Data
Rated Impulse Voltage
Insulation material group /
Gauge pin code according to IEC 60947-1
Protection class / Protection conductor type

Ordering Data
Beige
Grey

Voltage, V ~	Current, A	Cross Section
800	17.5	1.5 mm ²

	0.34 - 2.5 mm ²
	0.34 - 1.5 mm ²
	0.5 mm ²
	AWG 22 - 14
	9 - 10 mm
	0.4 x 2.5

	8/3
	1/A1 - B1
	IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD1.5SDBEIGE	70	EPPFD1.5SDBEIGE	100
PFD1.5SDGREY	70	EPPFD1.5SDGREY	100

Voltage, V ~	Current, A	Cross Section
		1.5 mm ²

	0.34 - 2.5 mm ²
	0.34 - 1.5 mm ²
	0.5 mm ²
	AWG 22 - 14
	9 - 10 mm
	0.4 x 2.5

	8/3
	1/A1 - B1
	IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD1.5PE	70	EPPFD1.5PE	100

Push In Cross Connection

Part Number	Qty.	Part Number	Qty.
CCS1.5/2	25		
CCS1.5/3	20		
CCS1.5/4	15		
CCS1.5/10	5		

Part Number	Qty.	Part Number	Qty.

End Bracket
xx: Beige or Grey

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Test Plug and Sockets

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.

Unprinted Markers

Part Number	Qty.	Part Number	Qty.
MT6/4	400		

Part Number	Qty.	Part Number	Qty.
MT6/4	400		

PFD1.5C

Width: 4.2 mm




75.10

37.80
MPR 35 x 7.5

1.5 mm² PushFit Feed Through Terminal Block
2 In, 2 Out
For 35 mm DIN Rail

PFD1.5CPE

Width: 4.2 mm



75.10

37.80
MPR 35 x 7.5

1.5 mm² PushFit Feed Through Terminal Block
2 In, 2 Out, Protective Earth
For 35 mm DIN Rail

PFD2.5E

Width: 5 mm




64.85

43.00
MPR 35 x 7.5

2.5 mm² PushFit Feed Through Terminal Block
1 In, 2 Out
For 35 mm DIN Rail

PFD2.5PE

Width: 5 mm



64.85

43.00
MPR 35 x 7.5

2.5 mm² PushFit Feed Through Terminal Block
1 In, 2 Out, Protective Earth
For 35 mm DIN Rail

Voltage, V ~	Current, A	Cross Section
800	17.5	1.5 mm ²

0.34 - 2.5 mm ²
0.34 - 1.5 mm ²
0.5 mm ²
AWG 22- 14
9 - 10 mm
0.4 x 2.5

8/3
1/A1 - B1
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD1.5CBEIGE	70	EPPFD1.5CBEIGE	100
PFD1.5CGREY	70	EPPFD1.5CGREY	100

Part Number	Qty.	Part Number	Qty.
CCS1.5/2	25		
CCS1.5/3	20		
CCS1.5/4	15		
CCS1.5/10	5		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
MT6/4	400		

Voltage, V ~	Current, A	Cross Section
		1.5 mm ²

0.34 - 2.5 mm ²
0.34 - 1.5 mm ²
0.5 mm ²
AWG 22 - 14
9 - 10 mm
0.4 x 2.5

8/3
1/A1 - B1
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD1.5CPE	70	EPPFD1.5CPE	100

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
MT6/4	400		

Voltage, V ~	Current, A	Cross Section
800	24	2.5 mm ²
600	20	AWG 22 - 12

0.34 - 4 mm ²
0.34 - 2.5 mm ²
0.5 mm ²
AWG 22 - 12
9 - 10 mm
0.4 x 2.5

8/3
1/A3
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD2.5EBEIGE	50	EPPFD2.5EBEIGE	10
PFD2.5EGREY	50	EPPFD2.5EGREY	10

Part Number	Qty.	Part Number	Qty.
CCS2.5/2	25		
CCS2.5/3	20		
CCS2.5/4	15		
CCS2.5/10	5		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
PFT	25		

Part Number	Qty.	Part Number	Qty.
DG10/5	440		
DG10/5T	440		
MT10/5	500		

Voltage, V ~	Current, A	Cross Section
		2.5 mm ²
		AWG 22 - 12

0.34 - 4 mm ²
0.34 - 2.5 mm ²
0.5 mm ²
AWG 22 - 12
9 - 10 mm
0.4 x 2.5

8/3
1/A3
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD2.5PE	50	EPPFD2.5PE	10

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		


Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
DG10/5	440		
DG10/5T	440		
MT10/5	500		

Multi Input & Multi Output Terminals Push Fit Connection

PFD2.5C


Width: 5 mm



2.5 mm² PushFit Feed Through Terminal Block
2 In, 2 Out
For 35 mm DIN Rail

PFD2.5CPE

Width: 5 mm



2.5 mm² PushFit Feed Through Terminal Block
2 In, 2 Out, Protective Earth
For 35 mm DIN Rail



Electrical Ratings
CE (EN 60947-7-1 - EN 60947-7-2)
cRUus
VDE (IEC 60947-7-1)
CSA
IECEX

Connection Data
Conductor cross section solid (min.-max.)
Conductor cross section stranded (min.-max.)
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, (min.-max.)
AWG Conductor
Insulation Stripping Length
Screwdriver

Technical Data
Rated Impulse Voltage
Insulation material group /
Gauge pin code according to IEC 60947-1
Protection class / Protection conductor type

Ordering Data
Beige
Grey

Voltage, V ~	Current, A	Cross Section
800	24	2.5 mm²
600	20	AWG 22 - 12

0.34 - 4 mm²
0.34 - 2.5 mm²
0.5 mm²
AWG 22 - 12
9 - 10 mm
0.4 x 2.5

8/3
1/A3
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD2.5CBEIGE	50	EPPFD2.5CBEIGE	10
PFD2.5CGREY	50	EPPFD2.5CGREY	10

Voltage, V ~	Current, A	Cross Section
		2.5 mm²
		AWG 22-12

0.34 - 4 mm²
0.34 - 2.5 mm²
0.5 mm²
AWG 22 - 12
9 - 10 mm
0.4 x 2.5

8/3
1/A3
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD2.5CPE	50	EPPFD2.5CPE	10

Push In Cross Connection

Part Number	Qty.	Part Number	Qty.
CCS2.5/2	25		
CCS2.5/3	20		
CCS2.5/4	15		
CCS2.5/10	5		

Part Number	Qty.	Part Number	Qty.

End Bracket
xx: Beige or Grey

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Test Plug and Sockets

Part Number	Qty.	Part Number	Qty.
PFT	25		

Part Number	Qty.	Part Number	Qty.


Unprinted Markers

Part Number	Qty.	Part Number	Qty.
DG10/5	440		
DG10/5T	440		
MT10/5	500		

Part Number	Qty.	Part Number	Qty.
DG10/5	440		
DG10/5T	440		
MT10/5	500		

PFD4E


Width: 6 mm



4 mm² PushFit Feed Through Terminal Block
1 In, 2 Out
For 35 mm DIN Rail

PFD4PE


Width: 6 mm



4 mm² PushFit Feed Through Terminal Block
1 In, 2 Out, Protective Earth
For 35 mm DIN Rail

PFD4C


Width: 6 mm



4 mm² PushFit Feed Through Terminal Block
2 In, 2 Out
For 35 mm DIN Rail

PFD4CPE

Width: 6 mm



4 mm² PushFit Feed Through Terminal Block
2 In, 2 Out, Protective Earth
For 35 mm DIN Rail

Voltage, V ~	Current, A	Cross Section
800	32	4 mm ²
600	30	AWG 22 - 10
800	30	

0.34 - 6 mm ²
0.25 - 4 mm ²
1.0 mm ²
AWG 22 - 10
9 - 10 mm
0.5 x 3.0

8/3
1/A4
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD4EBEIGE	50	EPPFD4EBEIGE	50
PFD4EGREY	50	EPPFD4EGREY	50

Part Number	Qty.	Part Number	Qty.
CCS4/2	25		
CCS4/3	20		
CCS4/4	15		
CCS4/10	5		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
PFT	25		

Part Number	Qty.	Part Number	Qty.
MT10/6	500		
DG10/6	360		

Voltage, V ~	Current, A	Cross Section
		4 mm ²

0.34 - 6 mm ²
0.25 - 4 mm ²
1.0 mm ²
AWG 22 - 10
9 - 10 mm
0.5 x 3.0

8/3
1/A4
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD4PE	50	EPPFD4PE	50

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
MT10/6	500		
DG10/6	360		

Voltage, V ~	Current, A	Cross Section
1000	32	4 mm ²

0.34 - 6 mm ²
0.25 - 4 mm ²
1.0 mm ²
AWG 22 - 10
9 - 10 mm
0.5 x 3.0

8/3
1/A4
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD4CBEIGE	45	EPPFD4CBEIGE	25
PFD4CGREY	45	EPPFD4CGREY	25

Part Number	Qty.	Part Number	Qty.
CCS4/2	25		
CCS4/3	20		
CCS4/4	15		
CCS4/10	5		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
PFT	25		

Part Number	Qty.	Part Number	Qty.
MT10/6	500		
DG10/6	360		

Voltage, V ~	Current, A	Cross Section
		4 mm ²

0.34 - 6 mm ²
0.25 - 4 mm ²
1.0 mm ²
AWG 22 - 10
9 - 10 mm
0.5 x 3.0

8/3
1/A4
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD4CPE	45	EPPFD4CPE	25

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		


Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
MT10/6	500		
DG10/6	360		

Multi Input & Multi Output Terminals Push Fit Connection

PFD6E


Width: 8 mm



6 mm² PushFit Feed Through Terminal Block
1 In, 2 Out
For 35 mm DIN Rail

PFD6PE

Width: 8 mm



6 mm² PushFit Feed Through Terminal Block
1 In, 2 Out, Protective Earth
For 35 mm DIN Rail



Electrical Ratings
CE (EN 60947-7-1 - EN 60947-7-2)
cRUus
VDE (IEC 60947-7-1)
CSA
IECEX

Connection Data
Conductor cross section solid (min.-max.)
Conductor cross section stranded (min.-max.)
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, (min.-max.)
AWG Conductor
Insulation Stripping Length
Screwdriver

Technical Data
Rated Impulse Voltage
Insulation material group /
Gauge pin code according to IEC 60947-1
Protection class / Protection conductor type

Ordering Data
Beige
Grey

Push In Cross Connection

End Bracket
xx: Beige or Grey

Test Plug and Sockets

Unprinted Markers

Voltage, V ~	Current, A	Cross Section
1000	41	6 mm²

0.5 - 10 mm²
0.5 - 6 mm²
1.5 mm²
AWG 20 - 8
11 - 13 mm
0.6 x 3.5

8/3
1/A5
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD6EBEIGE	45	EPPFD6EBEIGE	25
PFD6EGREY	45	EPPFD6EGREY	25

Part Number	Qty.	Part Number	Qty.
CCS6/2	25		
CCS6/3	20		
CCS6/4	15		
CCS6/10	5		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
PFT	25		

Part Number	Qty.	Part Number	Qty.
DG10/5	360		
DG10/6	360		

Voltage, V ~	Current, A	Cross Section
		6 mm²

0.5 - 10 mm²
0.5 - 6 mm²
1.5 mm²
AWG 20 - 8
11 - 13 mm
0.6 x 3.5

8/3
1/A5
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD6PE	45	EPPFD6PE	25

Part Number	Qty.	Part Number	Qty.


Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
DG10/5	360		
DG10/6	360		

PFD6C


Width: 8 mm



6 mm² PushFit Feed Through Terminal Block
2 In, 2 Out
For 35 mm DIN Rail

PFD6CPE

Width: 8 mm



6 mm² PushFit Feed Through Terminal Block
2 In, 2 Out, Protective Earth
For 35 mm DIN Rail

Voltage, V ~	Current, A	Cross Section
1000	41	6 mm ²

0.5 - 10 mm ²
0.5 - 6 mm ²
1.5 mm ²
AWG 20 - 8
11 - 13 mm
0.6 x 3.5

8/3
1/A5
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD6CBEIGE	35	EPPFD6CBEIGE	25
PFD6CGREY	35	EPPFD6CGREY	25

Part Number	Qty.	Part Number	Qty.
CCS6/2	25		
CCS6/3	20		
CCS6/4	15		
CCS6/10	5		

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.
PFT	25		

Part Number	Qty.	Part Number	Qty.
DG10/5	360		
DG10/6	360		

Voltage, V ~	Current, A	Cross Section
		6 mm ²

0.5 - 10 mm ²
0.5 - 6 mm ²
1.5 mm ²
AWG 20 - 8
11 - 13 mm
0.6 x 3.5

8/3
1/A5
IP 20/ -

Terminal	Qty.	End Plate	Qty.
PFD6CPE	35	EPPFD6CPE	25

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
ES1xx	100		
ES4xx	100		
ES7xx	50		

Part Number	Qty.	Part Number	Qty.

Part Number	Qty.	Part Number	Qty.
DG10/5	360		
DG10/6	360		



PUSH THE BUTTONS OF EXCELLENCE.

Designed and manufactured in Western Europe, IMO's comprehensive high quality range of modular 22.5mm and 30mm push buttons and controls provide a flexible, reliable system for operating low voltage electrical systems. Encompassing a myriad of switching options from momentary push and e-stops to multi-position captive key switches and the ability to mix, match and stack contact blocks, they offer the ultimate level of flexibility and customisation .

Additional accessories including high brightness LED pilot lights and switch illumination options, actuator engraving, collars, legend plates, protective shrouds and pre-drilled enclosures add a smart, professional look and additional functionality to the range. Environmental protection up to IP67 is available with most parts, making them suitable for both interior and exterior use.

Make the right selection; Switch to IMO Precision Controls

- IP67/IP65 Protection
- Maintained or Spring Return
- Opaque or Illuminated
- Assembled Control Stations
- Aluminium, Black or Chrome Bezel
- 1/2/3 Hole Push Button Enclosure
- Snap-On Contact Blocks
- Key Operated Switch
- Colour Coded Contacts
- Labelling Accessories
- International Approvals including UL Approved Products



Scan this QR code using your smartphone to view our **Push Buttons Range**