

IQ1300MM 120V/60HZ CAPACITY CHART

WATTS BTU/HR

733 2500


586 2000

440 1500

293 1000

147 500

0 0



77°F/25°C

95°F/35°C

113°F/45°C

131°F/55°C

AMBIENT TEMPERATURE

77 83 89 95 101 107 113 119 125 131 °F

25.0 28.3 31.7 35.0 38.3 41.7 45.0 48.3 51.7 55.0 °C

RETURN AIR TEMPERATURE

IQ1300MM 230V/60HZ CAPACITY CHART

WATTS BTU/HR

733 2500


586 2000

440 1500

293 1000

147 500

0 0



77°F/25°C

95°F/35°C

113°F/45°C

131°F/55°C

AMBIENT TEMPERATURE

77 83 89 95 101 107 113 119 125 131 °F


25.0 28.3 31.7 35.0 38.3 41.7 45.0 48.3 51.7 55.0 °C

RETURN AIR TEMPERATURE

IQ1300MM 24VDC CAPACITY CHART

WATTS BTU/HR

733 2500
586 2000
440 1500
293 1000
147 500
0 0



77°F/25°C
95°F/35°C
113°F/45°C
131°F/55°C

AMBIENT TEMPERATURE

77 83 89 95 101 107 113 119 125 131 °F
25.0 28.3 31.7 35.0 38.3 41.7 45.0 48.3 51.7 55.0 °C

RETURN AIR TEMPERATURE

IQ1300MM 48VDC CAPACITY CHART

WATTS BTU/HR

733 2500


586 2000

440 1500

293 1000

147 500

0 0



77°F/25°C

95°F/35°C

113°F/45°C

131°F/55°C

AMBIENT TEMPERATURE

77 83 89 95 101 107 113 119 125 131 °F

25.0 28.3 31.7 35.0 38.3 41.7 45.0 48.3 51.7 55.0 °C

RETURN AIR TEMPERATURE