



M-6064 5



CAT NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.	CONFIGURATION	RATING	HOUSING	
			MATERIAL	COLOR				MATERIAL	COLOR
					HBL3100C7W		100 A 480 VAC	NYLON	RED
					HBL3100C8V0DC		100 A 550 VDC	PBT	BLACK
HBL3100C4W		100 A 125 VAC	NYLON	YELLOW					
HBL3100C6W		100 A 250 VAC	NYLON	BLUE					
HBL3125C6W		125 A 220-240 VAC							

NOTES: (UNLESS OTHERWISE SPECIFIED)

1) TOLERANCES ARE:
 DECIMALS $\pm .03$
 ANGLES $\pm 2^\circ$

2) DIMENSIONS ARE INCHES
 [MILLIMETERS]

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
INTERIOR	THERMOSET	
SLEEVES	BRASS	
INSERT SPRINGS	BERR COPPER	SILVER
TERM. SCRS.	STAIN. STEEL	
COVER	POLYESTER	
COV. SCR.	BRASS	NICKEL
COV. SPR.	STAIN. STEEL	
GASKET	NEOPRENE	
DISC	POLYCARBONATE	
ARM	POLYESTER	
HINGE PIN	STAIN. STEEL	
HINGE SPR.	STAIN. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASS'Y SCRS	STAIN. STEEL	

5	ADDED POLARITY TO HBL3100C8V0DC, PER DCN16648 MYA	TLS	TLS	5/4/10
4	ADDED CAT. HBL3100C8V0DC PER DCN 16502 SPN TLS		MJM	4/12/10
3	REDRAWN ON CAD WITH CHANGES, ADDED "HOUSING" AND "COMMENTS" COLUMNS TO TABLE, "& 125A TO DWG TITLE AND NOTES 1 & 2, IN TABLE, REMOVED CAT NO'S 3100C3W, & 3100C5W AND C31009W; "A" WAS "AMP" IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER" IN (2) PLACES, "CABLE ϕ 1.065 [27.05] MIN. ϕ 1.940 [49.25] MAX" WAS "CABLE DIA. 1.125 28.57MM MIN. 1.650 41.91MM MAX" "Ø" WAS "DIA." AND "(XX.X)" WAS "MM", SUPERSEDES DRAWING DATED 5/9/80 PER DCN #12944. JMN		DJP	5/14/06

SYM REVISIONS APP DATE

THE DESIGN AND DIMENSIONS OF THE
 PRODUCT SHOWN ON THIS DRAWING ARE
 SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 100A & 125A 2 POLE 3 WIRE
 PIN AND SLEEVE
 CONNECTOR

TOLERANCES UNLESS
 OTHERWISE SPECIFIED
 FRACTIONS $\pm 1/64$
 DECIMALS $\pm .005$
 ANGLES $\pm 2^\circ$

WIRING DEVICE-KELLEMS
 HUBBELL INCORPORATED
 BRIDGEPORT, CT

DR. BY MJK APP. BY DJP
 TR. BY JMN SCALE NONE
 CHK'D BY DJP DATE 6/14/06

DIMENSION SHEET FOR CAT. NO.

SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☐

B

M-6064

5