



M-6068 4



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
INTERIOR	THERMOSET	
SLEEVES	BRASS	
SLEEVE SPRINGS	ST. STEEL	
TERMINAL SCREWS	ST. STEEL	
COVER	POLYESTER	
COVER SCREW	BRASS	NICKEL
COVER SPRING	ST. STEEL	
GASKET	NEOPRENE	
DISC	POLYCARBONATE	
ARM	POLYESTER	
HINGE PIN	ST. STEEL	
HINGE SPRING	ST. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSEMBLY SCREWS	ST. STEEL	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐

NON-REPAIRABLE ☒

B

M-6068

4

CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING		CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR					MATERIAL	COLOR
						HBL420C7W		20 A 3Ø 480 VAC		NYLON	RED
						HBL420C9W		20 A 3Ø 250 VAC		NYLON	BLUE
HBL420C5W		20 A 3Ø 600 VAC		NYLON	BLACK						
HBL416C6W		16 A 380-415 VAC		NYLON	RED	HBL420C12W		20 A 125/250 VAC		NYLON	ORANGE

NOTES (UNLESS OTHERWISE SPECIFIED)

1) TOLERANCES ARE:

DECIMALS ± .03
ANGLES ± 2°

2) DIMENSIONS ARE: INCHES
[MILLIMETERS]

4	REDRAWN ON CAD WITH CHANGES. ADDED "HOUSING" & "COMMENTS" COLUMNS, TO TABLE, AND NOTES 1 & 2. IN TABLE, "380 - 415VAC" WAS "380VAC" AND "A" WAS "AMP". "7.90 [200.7]" WAS "7.90 203.3MM". IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER" IN (2) PLACES. "CABLE Ø.330[8.4] MIN./Ø.830 [21.08] MAX" WAS "CABLE DIA. .390 9.9MM MIN. Ø.830[21.08] MAX". "Ø" WAS "DIA." AND "[XX.X]" WAS "MM". SUPERSEDES DRAWING DATED 4/30/80 PER DCN #12944. JMN	DJP	6/14/06
---	--	-----	---------

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
16A & 20A 3 POLE 4 WIRE
PIN AND SLEEVE CONNECTORS

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	1/64	DR. BY	MJK
DECIMALS	± .005	APP. BY	DJP
ANGLES	± 2°	TR. BY	JMN
		CHK'D BY	DJP
		SCALE	NONE
		DATE	6/14/06