



M-6084 5



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
INTERIOR	THERMOSET	
SLEEVES	BRASS*	
SLEEVE SPRINGS	ST. STEEL	
TERMINAL SCREWS	ST. STEEL	
COVER	POLYESTER	
COVER SCREW	BRASS	NICKEL
COVER SPRING	ST. STEEL	
GASKET	NEOPRENE	
DISC	POLYCARBONATE	
ARM	POLYESTER	
HINGE PIN	ST. STEEL	
HINGE SPRING	ST. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSEMBLY SCREWS	ST. STEEL	
*CONTACTS NICKEL PLATED BRASS		

CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING		CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR					MATERIAL	COLOR
HBL516C1W*		16 A		NYLON	BLUE	HBL520C7W		20 A 3ØY 277/480 VAC		NYLON	RED
						HBL520C9W		20 A 3ØY 120/208 VAC		NYLON	BLUE
HBL520C5W		20 A 3ØY 347/600 VAC		NYLON	BLACK						
HBL516C6W		16A 220/380VAC 240/415 VAC		NYLON	RED						

NOTES (UNLESS OTHERWISE SPECIFIED)
 1) TOLERANCES ARE:
 DECIMALS ± .03
 ANGLES ± 2°
 2) DIMENSIONS ARE: INCHES
 [MILLIMETERS]

5	REDRAWN ON CAD WITH CHANGES. ADDED "HOUSING" & "COMMENTS" COLUMNS TO TABLE, AND NOTES 1 & 2. IN TABLE, ADDED "16A" TO HBL516C1W, "240/415VAC" TO HBL516C6W AND "A" WAS "AMP". IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER" IN (2) PLACES. ADDED "CONTACTS NICKEL PLATED BRASS". "CABLE Ø.330[8.4] MIN./Ø.830 [21.08] MAX" WAS "CABLE DIA. .550/13.97MM MIN. .870[22.09] MAX". "Ø" WAS "DIA." AND "[XX.X]" WAS "MM". "[XX.X]" WAS "MM". SUPERSEDES DRAWING DATED 4/30/80 PER DCN #12944. JMN	DJP	6/27/06
---	--	-----	---------

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 16A & 20A 4 POLE 5 WIRE
 PIN AND SLEEVE CONNECTORS

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS 1/64 DECIMALS ± .005 ANGLES ± 2°		WIRING DEVICE—KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
DR. BY	MJK	APP. BY	DJP
TR. BY	JMN	SCALE	NONE
CHK'D BY	DJP	DATE	6/27/06

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6084

5