



M-6088 6



CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING		CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR					MATERIAL	COLOR
						HBL530C7W		30A 3ØY 277/480 VAC		NYLON	RED
						HBL530C9W		30A 3ØY 120/208 VAC		NYLON	BLUE
HBL530C5W		30A 3ØY 347/600 VAC		NYLON	BLACK						
HBL532C6W		32A 220/380VAC 240/415 VAC		NYLON	RED						
HBL530C6V02		30A 220/380VAC 240/415 VAC		VALOX	RED						

NOTES (UNLESS OTHERWISE SPECIFIED)
 1) TOLERANCES ARE:
 DECIMALS ± .03
 ANGLES ± 2°
 2) DIMENSIONS ARE: INCHES
 [MILLIMETERS]

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
INTERIOR	THERMOSET	
SLEEVES	BRASS	
PH. & NEUT. SPRGS.	ST. STEEL	
GRD. INSERT	BERR. COPPER	SILVER
TERMINAL SCREWS	ST. STEEL	
COVER	POLYESTER	
COVER SCREW	BRASS	NICKEL
COVER SPRING	ST. STEEL	
GASKET	NEOPRENE	
DISC	POLYCARBONATE	
ARM	POLYESTER	
HINGE PIN	ST. STEEL	
HINGE SPRING	ST. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSEMBLY SCREWS	ST. STEEL	

6	ADDED CAT. # HBL530C6V02 AND SPECS. TO TABLE. PER DCN 18699 DDL	CAC	04/24/12
5	REDRAWN ON CAD WITH CHANGES. ADDED "HOUSING" & "COMMENTS" COLUMNS TO TABLE, AND NOTES 1 & 2. IN TABLE, REMOVED CAT. NO. HBL530C2W, & ADDED "240/415VAC TO CAT. NO. HBL532C6W; "A" WAS "AMP". IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER" IN (2) PLACES. "CABLE Ø.500 [12.70] MIN. / Ø1.450 [36.80] MAX" WAS "CABLE DIA. .700/17.78MM MIN. 1.350 [34.29] MAX". "Ø" WAS "DIA." AND "XX.X" WAS "MM". "XX.X" WAS "MM". SUPERSEDES DRAWING DATED 5/7/80 PER DCN #12944. JMN	DJP	6/28/06

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 30A & 32A 4 POLE 5 WIRE
 PIN AND SLEEVE CONNECTORS

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE—KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT			
FRACTIONS ± 1/64	DR. BY	MJK	APP. BY	DJP
DECIMALS ± .005	TR. BY	JMN	SCALE	NONE
ANGLES ± 2°	CHK'D BY	DJP	DATE	6/28/06