

MP

Module Plates



MP Applications

Product Description


The module plates have cut-outs for fixing the KEL range cable entry systems KEL 24, KEL-U 24, KEL-JUMBO, KEL-DPF, KEL-JUMBO flex and KEL-ULTRA flex.

The module plates can be fixed on:

- Separation walls by Rittal
- closed enclosure bases and roofs (various manufacturers)
- Bases of Lohmeier enclosures
- Bases of Rittal enclosures via KDR-BMP base plates

The module blank plate without cut-outs (Order No. 43882) is designed for closing unused cut-outs. This module plate can even be used for self-made cut-outs.

Module plates are supplied with a gasket.



Cable routing via module plates in the base of a Rittal TS 8 enclosure. Mounting with icotek base plate KDR BMP.



Cable routing through the divider panel of a Rittal TS8 baying enclosure system via module plates.




Routing of several cables with and without connectors through a closed enclosure roof via module plates. Cut-out size 314 x 144 mm.



Routing of a rigid supply line through a closed enclosure roof via module plates. Cut-out size 314 x 144 mm.

MP Module Plates



Description	Type	Order No.	Compatible with
-------------	------	-----------	-----------------

	MP 0	43882	Module plate, blank
	MP 1	43891	3x KEL(-U) 24 x
	MP 2	43890	4x KEL(-U) 24 x
	MP 3	43886	1x KEL-JUMBO 1 1x KEL-JUMBO 2
	MP 4	43888	2x KEL-JUMBO 1
	MP 5	43887	2x KEL(-U) 24 x 1x KEL-JUMBO 1
	MP 6	43883	5x cut-out M50 for KEL-DPF or KEL-DPZ
	MP 7	43889	Cut-out 3x KEL-JUMBO flex
	MP 8	43894	Cut-out 2x KEL-ULTRA flex

Specifications

Material	Carbon steel, zinc-plated Aluminum (Order No. 43883)
Dimension	338 x 168 x 2 mm

Compatible with

KEL 24 Cable entry frames	18
KEL-U 24 Cable entry frames	8
KEL-SNAP snap frames	36 - 37
KEL-JUMBO Cable entry frames	34
KEL-DPF Cable entry grommets	77
KEL-JUMBO flex Cable entry ins.	78
KEL-ULTRA flex Cable entry ins.	79
Blank plates	158 - 160