



Reversing switches, T0, 20 A, surface mounting, 3 contact unit(s),  
Contacts: 5, 60 °, maintained, With 0 (Off) position, 1-0-2, design no. 8401



Part no. T0-3-8401/I1  
Catalog No. 207132

EL-Nummer 0001456427  
(Norway)



Similar to illustration

## Delivery program

|                                                    |                |                 |                                                                                 |
|----------------------------------------------------|----------------|-----------------|---------------------------------------------------------------------------------|
| Product range                                      |                |                 | Control switches                                                                |
| Part group reference                               |                |                 | T0                                                                              |
| Basic function                                     |                |                 | Reversing switches                                                              |
|                                                    |                |                 | with black thumb grip and front plate                                           |
| Contacts                                           |                |                 | 5                                                                               |
| Degree of Protection                               |                |                 | IP65                                                                            |
|                                                    |                |                 | <b>totally insulated</b>                                                        |
| Design                                             |                |                 | surface mounting                                                                |
|                                                    |                |                 |                                                                                 |
| Contact sequence                                   |                |                 |                                                                                 |
| Switching angle                                    |                | °               | 60                                                                              |
| Switching performance                              |                |                 | maintained<br>With 0 (Off) position                                             |
| Design number                                      |                |                 | 8401                                                                            |
| Front plate no.                                    |                |                 | <br><b>FS 684</b>                                                               |
| front plate                                        |                |                 | 1-0-2                                                                           |
| <b>Motor rating AC-23A, 50 - 60 Hz</b>             |                |                 |                                                                                 |
| 400 V                                              | P              | kW              | 5.5                                                                             |
| Rated uninterrupted current                        | I <sub>u</sub> | A               | 20                                                                              |
| Note on rated uninterrupted current I <sub>u</sub> |                |                 | Rated uninterrupted current I <sub>u</sub> is specified for max. cross-section. |
| Number of contact units                            |                | contact unit(s) | 3                                                                               |

## Technical data

### General

|           |  |  |                                                                                         |
|-----------|--|--|-----------------------------------------------------------------------------------------|
| Standards |  |  | IEC/EN 60947, VDE 0660, IEC/EN 60204<br>Switch-disconnector according to IEC/EN 60947-3 |
|-----------|--|--|-----------------------------------------------------------------------------------------|

|                                       |                  |      |                                                                                |
|---------------------------------------|------------------|------|--------------------------------------------------------------------------------|
| Climatic proofing                     |                  |      | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30 |
| Ambient temperature                   |                  |      |                                                                                |
| Enclosed                              |                  | °C   | -25 - +40                                                                      |
| Overvoltage category/pollution degree |                  |      | III/3                                                                          |
| Rated impulse withstand voltage       | U <sub>imp</sub> | V AC | 6000                                                                           |
| Mechanical shock resistance           |                  | g    | 15                                                                             |
| Mounting position                     |                  |      | As required                                                                    |

## Contacts

|                                                            |                 |                  |                                                                                 |
|------------------------------------------------------------|-----------------|------------------|---------------------------------------------------------------------------------|
| Electrical characteristics                                 |                 |                  |                                                                                 |
| Rated operational voltage                                  | U <sub>e</sub>  | V AC             | 690                                                                             |
| Rated uninterrupted current                                | I <sub>u</sub>  | A                | 20                                                                              |
| Note on rated uninterrupted current I <sub>u</sub>         |                 |                  | Rated uninterrupted current I <sub>u</sub> is specified for max. cross-section. |
| Load rating with intermittent operation, class 12          |                 |                  |                                                                                 |
| AB 25 % DF                                                 |                 | x I <sub>e</sub> | 2                                                                               |
| AB 40 % DF                                                 |                 | x I <sub>e</sub> | 1.6                                                                             |
| AB 60 % DF                                                 |                 | x I <sub>e</sub> | 1.3                                                                             |
| Short-circuit rating                                       |                 |                  |                                                                                 |
| Fuse                                                       |                 | A gG/gL          | 20                                                                              |
| Rated short-time withstand current (1 s current)           | I <sub>cw</sub> | A <sub>rms</sub> | 320                                                                             |
| Note on rated short-time withstand current I <sub>cw</sub> |                 |                  | Current for a time of 1 second                                                  |
| Rated conditional short-circuit current                    | I <sub>q</sub>  | kA               | 6                                                                               |

## Switching capacity

|                                                                         |                |                   |       |
|-------------------------------------------------------------------------|----------------|-------------------|-------|
| cos φ rated making capacity as per IEC 60947-3                          |                | A                 | 130   |
| Rated breaking capacity cos φ to IEC 60947-3                            |                | A                 |       |
| 230 V                                                                   |                | A                 | 100   |
| 400/415 V                                                               |                | A                 | 110   |
| 500 V                                                                   |                | A                 | 80    |
| 690 V                                                                   |                | A                 | 60    |
| Safe isolation to EN 61140                                              |                |                   |       |
| between the contacts                                                    |                | V AC              | 440   |
| Current heat loss per contact at I <sub>e</sub>                         |                | W                 | 0.6   |
| Current heat loss per auxiliary circuit at I <sub>e</sub> (AC-15/230 V) |                | CO                | 0.6   |
| Lifespan, mechanical                                                    | Operations     | x 10 <sup>6</sup> | > 0.4 |
| Maximum operating frequency                                             | Operations/h   |                   | 1200  |
| AC                                                                      |                |                   |       |
| AC-3                                                                    |                |                   |       |
| Rating, motor load switch                                               | P              | kW                |       |
| 220 V 230 V                                                             | P              | kW                | 3     |
| 230 V Star-delta                                                        | P              | kW                | 5.5   |
| 400 V 415 V                                                             | P              | kW                | 5.5   |
| 400 V Star-delta                                                        | P              | kW                | 7.5   |
| 500 V                                                                   | P              | kW                | 5.5   |
| 500 V Star-delta                                                        | P              | kW                | 7.5   |
| 690 V                                                                   | P              | kW                | 4     |
| 690 V Star-delta                                                        | P              | kW                | 5.5   |
| Rated operational current motor load switch                             |                |                   |       |
| 230 V                                                                   | I <sub>e</sub> | A                 | 11.5  |
| 230 V star-delta                                                        | I <sub>e</sub> | A                 | 20    |
| 400V 415 V                                                              | I <sub>e</sub> | A                 | 11.5  |
| 400 V star-delta                                                        | I <sub>e</sub> | A                 | 20    |
| 500 V                                                                   | I <sub>e</sub> | A                 | 9     |
| 500 V star-delta                                                        | I <sub>e</sub> | A                 | 15.6  |
| 690 V                                                                   | I <sub>e</sub> | A                 | 4.9   |

|                                               |                   |                |                                                                  |
|-----------------------------------------------|-------------------|----------------|------------------------------------------------------------------|
| 690 V star-delta                              | I <sub>e</sub>    | A              | 8.5                                                              |
| AC-23A                                        |                   |                |                                                                  |
| Motor rating AC-23A, 50 - 60 Hz               | P                 | kW             |                                                                  |
| 230 V                                         | P                 | kW             | 3                                                                |
| 400 V 415 V                                   | P                 | kW             | 5.5                                                              |
| 500 V                                         | P                 | kW             | 7.5                                                              |
| 690 V                                         | P                 | kW             | 5.5                                                              |
| Rated operational current motor load switch   |                   |                |                                                                  |
| 230 V                                         | I <sub>e</sub>    | A              | 13.3                                                             |
| 400 V 415 V                                   | I <sub>e</sub>    | A              | 13.3                                                             |
| 500 V                                         | I <sub>e</sub>    | A              | 13.3                                                             |
| 690 V                                         | I <sub>e</sub>    | A              | 7.6                                                              |
| DC                                            |                   |                |                                                                  |
| DC-1, Load-break switches L/R = 1 ms          |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 10                                                               |
| Voltage per contact pair in series            |                   | V              | 60                                                               |
| DC-21A                                        | I <sub>e</sub>    | A              |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 1                                                                |
| Contacts                                      |                   | Quantity       | 1                                                                |
| DC-23A, motor load switch L/R = 15 ms         |                   |                |                                                                  |
| 24 V                                          |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 10                                                               |
| Contacts                                      |                   | Quantity       | 1                                                                |
| 48 V                                          |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 10                                                               |
| Contacts                                      |                   | Quantity       | 2                                                                |
| 60 V                                          |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 10                                                               |
| Contacts                                      |                   | Quantity       | 3                                                                |
| 120 V                                         |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 5                                                                |
| Contacts                                      |                   | Quantity       | 3                                                                |
| 240 V                                         |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 5                                                                |
| Contacts                                      |                   | Quantity       | 5                                                                |
| DC-13, Control switches L/R = 50 ms           |                   |                |                                                                  |
| Rated operational current                     | I <sub>e</sub>    | A              | 10                                                               |
| Voltage per contact pair in series            |                   | V              | 32                                                               |
| Control circuit reliability at 24 V DC, 10 mA | Fault probability | H <sub>F</sub> | < 10 <sup>-5</sup> , < 1 failure in 100,000 switching operations |

### Terminal capacities

|                                      |  |                 |                                      |
|--------------------------------------|--|-----------------|--------------------------------------|
| Solid or stranded                    |  | mm <sup>2</sup> | 1 x (1 - 2,5)<br>2 x (1 - 2,5)       |
| Flexible with ferrules to DIN 46228  |  | mm <sup>2</sup> | 1 x (0.75 - 2.5)<br>2 x (0.75 - 2.5) |
| Terminal screw                       |  |                 | M3.5                                 |
| Tightening torque for terminal screw |  | Nm              | 1                                    |

### Technical safety parameters:

|       |  |  |                                                         |
|-------|--|--|---------------------------------------------------------|
| Notes |  |  | B10 <sub>d</sub> values as per EN ISO 13849-1, table C1 |
|-------|--|--|---------------------------------------------------------|

### Rating data for approved types

|                   |  |       |      |
|-------------------|--|-------|------|
| Terminal capacity |  |       |      |
| Terminal screw    |  |       | M3.5 |
| Tightening torque |  | lb-in | 8.83 |

## Design verification as per IEC/EN 61439

|                                        |  |  |  |
|----------------------------------------|--|--|--|
| Technical data for design verification |  |  |  |
|----------------------------------------|--|--|--|


|                                                                                                                        |                   |    |                                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------------|-------------------|----|----------------------------------------------------------------------------------------------------------------------------------|
| Rated operational current for specified heat dissipation                                                               | I <sub>n</sub>    | A  | 20                                                                                                                               |
| Heat dissipation per pole, current-dependent                                                                           | P <sub>vid</sub>  | W  | 0.6                                                                                                                              |
| Equipment heat dissipation, current-dependent                                                                          | P <sub>vid</sub>  | W  | 0                                                                                                                                |
| Static heat dissipation, non-current-dependent                                                                         | P <sub>vs</sub>   | W  | 0                                                                                                                                |
| Heat dissipation capacity                                                                                              | P <sub>diss</sub> | W  | 0                                                                                                                                |
| Operating ambient temperature min.                                                                                     |                   | °C | -25                                                                                                                              |
| Operating ambient temperature max.                                                                                     |                   | °C | 40                                                                                                                               |
| IEC/EN 61439 design verification                                                                                       |                   |    |                                                                                                                                  |
| 10.2 Strength of materials and parts                                                                                   |                   |    |                                                                                                                                  |
| 10.2.2 Corrosion resistance                                                                                            |                   |    | Meets the product standard's requirements.                                                                                       |
| 10.2.3.1 Verification of thermal stability of enclosures                                                               |                   |    | Meets the product standard's requirements.                                                                                       |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat                                             |                   |    | Meets the product standard's requirements.                                                                                       |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |                   |    | Meets the product standard's requirements.                                                                                       |
| 10.2.4 Resistance to ultra-violet (UV) radiation                                                                       |                   |    | UV resistance only in connection with protective shield.                                                                         |
| 10.2.5 Lifting                                                                                                         |                   |    | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.2.6 Mechanical impact                                                                                               |                   |    | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.2.7 Inscriptions                                                                                                    |                   |    | Meets the product standard's requirements.                                                                                       |
| 10.3 Degree of protection of ASSEMBLIES                                                                                |                   |    | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.4 Clearances and creepage distances                                                                                 |                   |    | Meets the product standard's requirements.                                                                                       |
| 10.5 Protection against electric shock                                                                                 |                   |    | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.6 Incorporation of switching devices and components                                                                 |                   |    | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.7 Internal electrical circuits and connections                                                                      |                   |    | Is the panel builder's responsibility.                                                                                           |
| 10.8 Connections for external conductors                                                                               |                   |    | Is the panel builder's responsibility.                                                                                           |
| 10.9 Insulation properties                                                                                             |                   |    |                                                                                                                                  |
| 10.9.2 Power-frequency electric strength                                                                               |                   |    | Is the panel builder's responsibility.                                                                                           |
| 10.9.3 Impulse withstand voltage                                                                                       |                   |    | Is the panel builder's responsibility.                                                                                           |
| 10.9.4 Testing of enclosures made of insulating material                                                               |                   |    | Is the panel builder's responsibility.                                                                                           |
| 10.10 Temperature rise                                                                                                 |                   |    | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating                                                                                             |                   |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility                                                                                    |                   |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function                                                                                              |                   |    | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## Technical data ETIM 7.0


|                                                                                                                                                                                                             |  |    |                  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----|------------------|
| Low-voltage industrial components (EG000017) / Off-load switch (EC001105)                                                                                                                                   |  |    |                  |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Changeover switch (ecl@ss10.0.1-27-37-14-05 [AKF062013]) |  |    |                  |
| Model                                                                                                                                                                                                       |  |    | Reversing switch |
| Number of poles                                                                                                                                                                                             |  |    | 3                |
| With 0 (off) position                                                                                                                                                                                       |  |    | Yes              |
| With retraction in 0-position                                                                                                                                                                               |  |    | No               |
| Rated permanent current I <sub>u</sub>                                                                                                                                                                      |  | A  | 20               |
| Rated operation current I <sub>e</sub> at AC-3, 400 V                                                                                                                                                       |  | A  | 11.5             |
| Rated operation power at AC-3, 400 V                                                                                                                                                                        |  | kW | 4                |
| Degree of protection (IP), front side                                                                                                                                                                       |  |    | IP65             |
| Degree of protection (NEMA), front side                                                                                                                                                                     |  |    | Other            |
| Number of auxiliary contacts as normally closed contact                                                                                                                                                     |  |    | 0                |
| Number of auxiliary contacts as normally open contact                                                                                                                                                       |  |    | 0                |
| Number of auxiliary contacts as change-over contact                                                                                                                                                         |  |    | 0                |
| Suitable for ground mounting                                                                                                                                                                                |  |    | Yes              |
| Suitable for front mounting 4-hole                                                                                                                                                                          |  |    | No               |
| Suitable for distribution board installation                                                                                                                                                                |  |    | No               |
| Suitable for intermediate mounting                                                                                                                                                                          |  |    | No               |

|                                               |  |                  |
|-----------------------------------------------|--|------------------|
| Complete device in housing                    |  | Yes              |
| Material housing                              |  | Plastic          |
| Type of control element                       |  | Toggle           |
| Type of electrical connection of main circuit |  | Screw connection |

**Dimensions**



M4



Drilling dimensions base