



Double-touch  
actuators, spring  
return - two flush  
pushbuttons  
LPSB71

Product designation

Product type designation

#### General characteristics

|                          |                                                                          |
|--------------------------|--------------------------------------------------------------------------|
| Colour                   | Black/Red                                                                |
| Material                 | Aluminium and zinc alloy for metal parts and polyamide for plastic parts |
| IEC degree of protection | IP66, IP67 and IP69K                                                     |

#### Mechanical features

|                  |                          |
|------------------|--------------------------|
| Fixing           | Without mounting adapter |
| Mounting adapter | LPXAU120M                |


#### UL technical data

|                         |                              |
|-------------------------|------------------------------|
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K |
|-------------------------|------------------------------|

#### Ambient conditions

|                       |     |    |     |
|-----------------------|-----|----|-----|
| Temperature           |     |    |     |
| Operating temperature |     |    |     |
|                       | min | °C | -25 |
|                       | max | °C | +70 |
| Storage temperature   |     |    |     |
|                       | min | °C | -40 |
|                       | max | °C | +85 |

#### Dimensions



#### Certifications and compliance

|            |                     |
|------------|---------------------|
| Compliance |                     |
|            | CSA C22.2 n° 14     |
|            | IEC/EN/BS 60947-1   |
|            | IEC/EN/BS 60947-5-1 |
|            | UL508               |

Certificates

cULus

#### ETIM classification

ETIM 8.0

EC000029 -  
Push-switch  
button