



Product designation

Miniature circuit
breaker (MCB)

Product type designation

P1 MB

Number of poles

2P

Number of DIN modules

2

Compliance

IEC / UL489

Electrical features

Rated insulation voltage Ui IEC/EN	V	440
Rated impulse withstand voltage Uimp	kV	4
Rated operational voltage AC (IEC)	VAC	230/400
Rated operational voltage AC (UL)	V	480Y/277
Rated operational voltage DC	VDC	125
Rated frequency	Hz	50/60
Rated current (In)	A	1.6
Tripping curve		C
Short circuit rating (IEC)	kA	10
Short circuit rating (UL)	kA	10
Electrical life	cycles	10000
Power dissipation per pole max	W	0.96

Ambient conditions

Operating temperature

min	°C	-40
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+80

Max altitude

m 2000

Mechanical features

Operating position

normal Vertical plan

Fixing

35mm DIN rail

Tightening torque for terminals

min	Nm	1.8
max	Nm	2
min	lbin	16
max	lbin	17.7

Terminals tool

Pz 2

Conductor section

IEC

min	mm ²	1
max	mm ²	35

AWG/Kcmil


min		14
max		6

Mechanical life


cycles 20000

Weight	g	255
Frontal IP degree		IP20
Pollution degree		2

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-2

UL489

Certifications

cULus

EAC

ETIM classification

ETIM 8.0

EC000042 -
Miniature circuit
breaker (MCB)