



Product designation
Product type designation

Auxiliary contact
11BGX10

Contact characteristics

Number of poles	Nr.	2	
Rated insulation voltage Ui IEC/EN	V	690	
Rated impulse withstand voltage Uimp	kV	6	
IEC Conventional free air thermal current Ith	A	10	
Tightening torque for terminals			
	min	Nm	0.8
	max	Nm	1
	min	lbin	9
	max	lbin	9

Tightening torque for coil terminal	min	lbin	9
	max	lbin	9

Max number of wires simultaneously connectable	Nr.	2
--	-----	---

Conductor section	AWG/Kcmil		
	max		12
Flexible w/o lug conductor section	min	mm ²	0.75
	max	mm ²	2.5
Flexible c/w lug conductor section	min	mm ²	0.75
	max	mm ²	2.5
Flexible with insulated spade lug conductor section	min	mm ²	0.75
	max	mm ²	2.5

Mechanical features

Operating position				normal allowable	On vertical plane Any
Fixing					Front centre mounting
Weight				g	21
Terminals screw					Screw
Conductor section				AWG/kcmil conductor section	
				max	12
IEC				max	mm ²
					1 or 2 x 2.5

Auxiliary contact characteristics

Type of contact		2NC
Thermal current I_{th}	A	10
IEC/EN 60947-5-1 designation		A600 - Q600

Operating current AC15	230V	A	3
	400V	A	1.9
	500V	A	1.4

Operating current DC13	24V	A	3
	48V	A	1.5
	60V	A	1.2
	110V	A	0.6
	125V	A	0.55
	220V	A	0.27
	600V	A	0.1

Electrical characteristics

Conductivity	5V 10 mA
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600

Operating current AC15	120V	A	6
	240V	A	3
	480V	A	1.5
	600V	A	1.2


Operating current DC13	12V	A	10
	250V	A	0.27
	440V	A	0.15
	500V	A	0.13

Ambient conditions


Temperature			
Operating temperature			
	min	°C	-50
	max	°C	+70
Storage temperature			
	min	°C	-60
	max	°C	+80

Max altitude	m	3000
--------------	---	------

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1
CSA C22.2 n° 60947-5-1
IEC/EN 60947-1
IEC/EN 60947-5-1
UL 60947-1
UL 60947-5-1

Certificates

CCC
cULus
EAC

ETIM classification

ETIM 8.0

EC000041 -
Auxiliary contact
block