



Product designation			Auxiliary contact			
Product type designation			11BGX10			
Contact characteristics						
Number of poles			Nr.	4		
Rated insulation voltage Ui IEC/EN			V	690		
Rated impulse withstand voltage Uimp			kV	6		
IEC Conventional free air thermal current Ith			A	10		
Tightening torque for terminals			min	Nm	0.8	
			max	Nm	1	
			min	Ibin	9	
			max	Ibin	9	
			Tightening torque for coil terminal			min
max	Ibin	9				
Max number of wires simultaneously connectable			Nr.	2		
Conductor section						
AWG/Kcmil			max		12	
			Flexible w/o lug conductor section			
			min	mm²	0.75	
			max	mm²	2.5	
Flexible c/w lug conductor section			min		mm²	0.75
			max		mm²	2.5
Flexible with insulated spade lug conductor section			min		mm²	0.75
			max		mm²	2.5
Mechanical features						
Operating position			normal		On vertical plane	
			allowable		Any	
Fixing			Front centre mounting			
Weight			g		28	
Terminals screw			Screw			
Conductor section						
AWG/kcmil conductor section			max		12	
			IEC			
			max	mm²	1 or 2 x 2.5	
Auxiliary contact characteristics						
Type of contact			1NO+3NC			
Thermal current Ith			A		10	
IEC/EN 60947-5-1 designation			A600 - Q600			

Operating current AC15

230V	A	3
400V	A	1.9
500V	A	1.4

Operating current DC13

24V	A	3
48V	A	1.5
60V	A	1.2
110V	A	0.6
125V	A	0.55
220V	A	0.27
600V	A	0.1

Electrical characteristics

Conductivity	5V 10 mA
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600

Operating current AC15

120V	A	6
240V	A	3
480V	A	1.5
600V	A	1.2

Operating current DC13

12V	A	10
250V	A	0.27
440V	A	0.15
500V	A	0.13

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	+70


Storage temperature

min	°C	-60
max	°C	+80


Max altitude

m	3000
---	------

Dimensions



Wiring diagrams



Certifications and compliance

Compliance	CSA C22.2 n° 60947-1
	CSA C22.2 n° 60947-5-1
	IEC/EN 60947-1
	IEC/EN 60947-5-1
	UL 60947-1
	UL 60947-5-1

Certificates	CCC
	cULus
	EAC

ETIM classification

ETIM 8.0	EC000041 - Auxiliary contact block
----------	--