



Product designation

LED elements
steady light
LPXLP

Product type designation

General characteristics

Colour	Red
--------	-----

Electrical characteristics

Supply voltage (AC)	V	185...265
---------------------	---	-----------

Supply voltage (DC)	V	185...265
---------------------	---	-----------

Operations

Electrical life	hours	100000
-----------------	-------	--------

Mechanical features

Tightening torque for terminals max	Nm	1
-------------------------------------	----	---

Conductor section

AWG/kcmil conductor section

max 12

IEC

max mm² 1 or 2 / 2.5

Mounting adapter	LPXAU120
------------------	----------

Weight	g	16
--------	---	----

Ambient conditions

Temperature


Operating temperature

min	°C	-25
max	°C	+70


Storage temperature

min	°C	-40
max	°C	+85

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

RINA

UL

ETIM classification

ETIM 8.0

EC000204 -
 Lamp holder
 block for control
 circuit devices