


Condenser Fan, Single Phase, PSC

5½ inch dia. MARS SERIES **098**



GE Commercial Motors

By Regal-Beloit



* Heat Shield




Vertical Outdoor Condenser Fan Motors Shaft-Up/Down

GE up/down outdoor condenser fan motors are designed for either vertical shaft-up or shaft-down applications. Shell and end shields are enclosed for weather protection. A weep hole is provided in each end shield to allow condensate to drain. A plastic plug is provided to seal the weep hole in the end shield exposed to the weather. All of these motors are suitable for air conditioning or heat pump applications. All feature reversible rotation, 208-230 volts, six inch shaft length and extended thru bolts extending from both ends.

Specifications:

- 60 Hertz
- Single phase
- Overload protected
- Fan duty, continuous, air over
- 26 inch leads
- Totally enclosed, non-ventilated
- Class B insulation



Features:

- Up/down design
- Thru bolt or band mounting
- All angle sleeve or ball bearings
- Water slinger on shaft
- Serrated end cap on shaft end only
- For air conditioning or heat pumps
- Full six inch shaft length with two full flats at 90°
- Reversible rotation
- For accessories, see pages M-73 to M-75

Reversible Rotation

MARS NO.	GE NO.	HP	VOLTS	AMPS	RPM	CAP REQ.	A	B	C
825 RPM - Single Speed - All Angle Sleeve Bearings - 8 Pole									
03725*	5KCP39DFAD06S	1/8	208-230	0.85	825	5/370	6.5	4.23	1/2
03403*	5KCP39HFAD05S	1/6	208-230	1.00	825	5/370	6.0	4.23	1/2
03404*	5KCP39JFAD07S	1/4	208-230	1.50	825	7.5/370	6.0	5.23	1/2
03405*	5KCP39NFAD09S	1/3	208-230	2.20	825	10/370	6.0	5.73	1/2
03746*	5KCP39TFAD10S	1/2	208-230	2.80	825	20/370	6.5	6.48	1/2

1075 RPM - Single Speed - Standard Efficiency - All Angle Sleeve Bearings - 6 Pole

03727	5KCP39DGS375S	1/6	208-230	1.00	1075	5/370	6.0	4.71	1/2
03727HS*	5KCP39DGY797S	1/6	208-230	1.00	1075	5/370	6.0	4.71	1/2
03728	5KCP39FGM599S	1/4	208-230	1.80	1075	5/370	6.0	4.25	1/2
03728HS*	5KCP39GGY769S	1/4	208-230	1.80	1075	5/370	6.0	4.25	1/2
03729	5KCP39LGS407S	1/3	208-230	2.30	1075	7.5/370	6.0	5.70	1/2
03729HS*	5KCP39LGY801S	1/3	208-230	2.30	1075	7.5/370	6.0	5.70	1/2
03759	5KCP39LGT378S	1/3	575	1.10	1075	7.5/370	6.0	5.75	1/2
03730	5KCP39PGS618S	1/2	208-230	3.50	1075	10/370	6.0	6.50	1/2
03730HS*	5KCP39RGY799S	1/2	208-230	3.50	1075	10/370	6.0	6.50	1/2
03760	5KCP39PGT377S	1/2	575	1.50	1075	7.5/370	6.0	5.75	1/2
03731	5KCP39SGT039S	3/4	208-230	4.70	1075	10/370	6.0	5.75	1/2
03731HS*	5KCP39SGY805S	3/4	208-230	4.70	1075	10/370	6.0	5.75	1/2