


CONNECTION DIAGRAM



PROVIDED WITH SAFE TOUCH TERMINAL COVERS.  
NO INTEGRAL FUSING CAPABILITY.

| DIMENSIONS     |               |               |               |              |               |                           | APPROX.WT.<br>LBS<br>(KG) |
|----------------|---------------|---------------|---------------|--------------|---------------|---------------------------|---------------------------|
|                | A             | B             | C             | D            | E             | MTG. SLOTS                |                           |
| INCHES<br>(MM) | 5.13<br>(130) | 5.25<br>(133) | 4.50<br>(114) | 3.88<br>(99) | 4.38<br>(111) | 0.313X1.063<br>(8.0X27.0) |                           |



|                       |      |             |                     |  |             |                                                                                                 |                                                                                                 |
|-----------------------|------|-------------|---------------------|--|-------------|-------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|
| CAT.NO. B500-2029-GAF |      |             | CONST. ENCAPSULATED |  |             |  LISTED    |                                                                                                 |
|                       |      |             | MODEL GLOBALTRAN    |  |             |                                                                                                 |                                                                                                 |
| RATING                |      |             |                     |  |             |                                                                                                 |  CERTIFIED |
| OUTPUT AMPS           | 20.8 | PRIMARY V   | 120X240             |  | TEMP. CLASS |  IEC 61558 |                                                                                                 |
| VA                    | 500  | SECONDARY V | 24                  |  | 130°C       |                                                                                                 |                                                                                                 |
|                       |      |             |                     |  |             | REVISION G                                                                                      |                                                                                                 |