

Features and Benefits – Hook and Loop Cable Ties

The comprehensive family of hook and loop cable ties delivers reliability by protecting against over-tensioning of high performance fiber and copper cables. These ties are adjustable, releasable, and re-usable to effectively support frequent moves, adds, and changes (MACs). A wide range of colors provides flexibility and an aesthetically pleasing appearance. The complete line of Panduit® Hook and Loop Cable Ties help maintain the reliable, scalable, and aesthetic requirements of data centers.

Tak-Ty® Hook & Loop Cable Ties – Premium, durable designs and sizes

Loop Style



Allows for pre-wrapping of bundles

Roll/Strip/Brick Style



Available in continuous or perforated rolls and stacked strips

Plenum-Rated



Distinctive maroon color (also available in black)

Tak-Tape™ Hook & Loop Rolls



Strong, low profile hook and loop material

Convenient packaging

Ultra-Cinch™ Hook & Loop Cable Ties



Unique same-sided material secures a greater range of bundle diameters

Available in three styles and eight colors; grommet styles used for bundle mounting applications

Low profile contoured cinch ring reduces overall bundle size



Wire management accessories speed and simplify the mounting of high performance cabling.

See pages B2.4, B2.10, B2.19, B2.22, C3.2, C3.3, C3.7, and C3.8.

Selection Guide – Hook and Loop Cable Ties



Product, Color (Suffix)	Style/Function	Part Number Prefix	Catalog Page
Tak-Ty® Ties, Black (0)	Loop Ties/Re-usable	HLT	B1.83
	Strip Ties/Re-usable	HLS	B1.83
	15' and 75' Rolls/Re-usable	HLM, HLS	B1.83
	Strip Ties/Re-usable/Brick	HLB	B1.83
Tak-Ty® Plenum-Rated Ties, UL Listed Black, Maroon (0, 12)	Loop Ties/Re-usable	HLTP	B1.84
	Strip Ties/Re-usable	HLSP	B1.84
Tak-Tape™ Rolls, Black (0)	20' and 35' Rolls/Re-usable	TTS	B1.84
Ultra-Cinch™ Ties, Black (0)	Cinch Ties/Re-usable	UCT	B1.85
	Cinch Ties – Center Mount Grommet/Re-usable	UGCTC	B1.85
	Cinch Ties – End Mount Grommet/Re-usable	UGCTE	B1.85

Part Number System for Hook and Loop Ties

<u>HLT</u>	<u>2</u>	<u>I</u>	<u>—</u>	<u>X</u>	<u>0</u>
Type	Size	Cross Section		Package Size	Color
HL = Hook and Loop	Approx.	I = Intermediate		X = 10	See Page B1.86
HLB = HL Brick	Maximum	S = Standard		C = 100	
HLM = HL Miniature	Bundle			15R = 15' Roll	
HLT = HL Loop Tie	Dia. (In.)			20R = 20' Roll	
HLTP = HL Loop Tie Plenum-Rated				35R3 = 35' Rolls (3)	
HLS = HL Strip Tie				35RX = 35' Rolls (10)	
HLSP = HL Strip Tie Plenum-Rated				75R = 75' Roll	
TTS = Tak-Tape™ Roll					
UCT = Ultra-Cinch™ Tie					
UGCTC = UCT Grommet Cinch Tie – Center Mount					
UGCTE = UCT Grommet Cinch Tie – End Mount					

A. System Overview

B1. Cable Ties

B2. Cable Accessories

B3. Stainless Steel Cable Ties & Accessories

C1. Wiring Duct

C2. Abrasion Protection

C3. Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems

E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Industrial Safety Solutions

F. Keystone Cabling Systems

G. Part Number Index

PANDUIT®

Industrial Electrical Solutions

Cable Tie Selection Chart

Follow this step-by-step process to find the cable ties that best suit your application:

Cable Tie Function

1) Select the main function of the cable tie you need:
Bundle = Standard Cable Ties
Re-use = Nylon Releasable Ties*
Identify = Marker and Flag Ties
Mount = Clamp Ties, Push Mount Ties, and Stud Mount Ties

Material Properties

2) Determine the appropriate material for your application:
Mechanical
Chemical
Thermal

Cable Tie Family

3) Select the cable tie family that meets your overall needs

	Cable Tie Function		Bundle, Re-use, Identify, Mount	Bundle, Re-use, Identify, Mount	Bundle, Re-use, Mount	Bundle, Re-use, Mount	Bundle	Bundle
				Weather Resistant Nylon 6.6	Impact Modified Weather Resistant Nylon 6.6	Heat Stabilized Nylon 6.6	Heat Stabilized Nylon 6.6	Heat Stabilized Weather Resistant Nylon 6.6
	Material	Test Method	Nylon 6.6	Weather Resistant Nylon 6.6	Impact Modified Weather Resistant Nylon 6.6	Heat Stabilized Nylon 6.6	Heat Stabilized Nylon 6.6	Heat Stabilized Weather Resistant Nylon 6.6
	Color	—	Natural	Black	Black	Black	Natural	Black
	Part Number Suffix (Material Designation)	—	No Suffix	0	0	30	39	300
Mechanical Properties	Tensile @ Yield @ 73°F (psi)	ISO 527	12,000	12,000	9,700	12,000	12,000	12,000
	Water Absorption (24 Hours)	ASTM D570	1.2%	1.2%	1.2%	1.2%	1.2%	1.2%
	Radiation Resistance (Rads)	—	1 x 10 ⁵	1 x 10 ⁵	1 x 10 ⁵	1 x 10 ⁵	1 x 10 ⁵	1 x 10 ⁵
	Weathering Life Expectancy (Years)/ UV Resistance	—	1 – 2	7 – 9	7 – 9	4 – 5	1 – 2	7 – 9
	Impact Resistance	—	○	○	⊖	○	○	○
	Chemical Resistance	Salts	—	●	●	●	●	●
Hydrocarbons (Gas, Oil, Lubricants)		—	●	●	●	●	●	●
Chlorinated Hydrocarbons		—	⊖	⊖	⊖	⊖	⊖	⊖
Acids		—	●	●	●	●	●	●
Bases		—	⊖	⊖	⊖	⊖	⊖	⊖
Acid Rain		—	●	●	●	●	●	●
Thermal Properties	Continuous Use Temperature Range	UL 746B	-76°F - 185°F -60°C - 85°C	-76°F - 185°F -60°C - 85°C	-76°F - 185°F -60°C - 85°C	-76°F - 239°F -60°C - 115°C	-76°F - 239°F -60°C - 115°C	-76°F - 239°F -60°C - 115°C
	Minimum Installation Temperature	UL 62275	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)
	Flammability Rating	UL 94	V-2	V-2	HB	V-2	V-2	V-2
	Low Smoke	ASTM E662	PASS	PASS	PASS	PASS	PASS	PASS
	Oxygen Index	BS ISO 4589	28	28	—	28	28	28
	Halogen-Free	IEC 60754-2	Yes	Yes	Yes	Yes	Yes	Yes
	Burning Fume Toxicity	BSS-7239	PASS	PASS	PASS	PASS	PASS	PASS
	Heat Deflection Temperature @ 1.8 Mpa	ASTM D648 ISO 75 -1/-2	158°F 70°C	158°F 70°C	145°F 63°C	158°F 70°C	158°F 70°C	158°F 70°C
Relative Price	—	Low	Low	Low	Low	Low	Med	

Cable Tie Catalog Page	Product Line			Cross Sections				
	Pan-Ty®		✓	SM, M, I, S	LH, H, EH	✓	✓	✓
	Super-Grip® (B1.38)		✓	M, I, S, LH	H	✓		
	Dome-Top® Barb Ty (B1.43)		✓	M, I, S	LH	✓	✓	✓
	Dura-Ty™ (B1.53)							
	Parallel-Entry (B1.56)		✓	M, I, S, HS	LH		✓	
	Sta-Strap® (B1. 65)		✓	M, I, S, LH, H		✓		
	Specialty Ties (B1.73)		✓		H	✓		✓

Check mark indicates material availability in that product line.

Cross Sections: SM = Subminiature, M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, EH = Extra-Heavy.

*For information on re-usable Hook and Loop Cable Ties, see page B1.81.

Order number of pieces required, in multiples of Standard Package Quantity.

Recommendation Legend	Highest	High	Acceptable	Low	Lowest

Bundle	Bundle, Identify	Bundle	Bundle	Bundle, Re-use	Bundle	Bundle	Bundle	Bundle	Bundle	Bundle
Flame Retardant Nylon 6.6	Flame Retardant Nylon 6.6	Weather Resistant Nylon 12	Polypropylene	Weather Resistant Polypropylene	TEFZEL ■	HALAR ▲	PEEK	Metal Detectable Nylon 6.6	Metal Detectable Polypropylene	Weather Resistant Acetal
Black	Natural Ivory	Black	Green	Black	Aqua Blue	Maroon	Brown	Blue	Blue	Black
60	69	120	109	100	76	702Y	71	86	186	N/A
11,000	11,000	6,700	4,100	4,100	7,500	7,000	15,200	—	—	6,500
1.1%	1.1%	0.3%	0.1%	0.1%	<0.03%	<0.05%	0.5%	1.2%	0.1%	<0.45%
1 x 10 ⁵	1 x 10 ⁵	3.5 x 10 ⁶	1 x 10 ⁶	1 x 10 ⁶	2 x 10 ⁸	2 x 10 ⁸	1 x 10 ⁹	—	1 x 10 ⁶	6 x 10 ⁵
1 – 2	1 – 2	12 – 15	1	7 – 9	>15	>15	—	—	1	>20
								—		
-76°F - 212°F -60°C - 100°C	-76°F - 212°F -60°C - 100°C	-76°F - 194°F -60°C - 90°C	-76°F - 239°F -60°C - 115°C	-76°F - 239°F -60°C - 115°C	-76°F - 338°F -60°C - 170°C	-76°F - 257°F -60°C - 125°C	-76°F - 257°F -60°C - 125°C	-76°F - 500°F -60°C - 260°C	-76°F - 239°F -60°C - 115°C	-76°F - 185°F -60°C - 85°C
-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)
V-0	V-0	HB	HB	HB	V-0	V-0	V-0	HB	HB	HB
PASS	PASS	—	—	—	—	—	PASS	—	—	PASS
34	34	—	—	—	30	52	35	—	—	—
Yes	Yes	Yes	Yes	Yes	No	No	Yes	Yes	Yes	Yes
PASS	PASS	—	—	—	—	—	—	—	—	—
154°F 68°C	154°F 68°C	122°F 50°C	122°F 50°C	122°F 50°C	—	149°F 65°C	313°F 156°C	145°F 63°C	122°F 50°C	239°F 115°C
Med	Med	Med	Med	Med	High	High	High	Low	Med	Med

✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	
	✓									
										✓
	✓									

Note 1: Check UL file for the specific part number rating

Note 2: Based upon UL RTI for electrical properties

■ TEFZEL is a registered trademark of E.I. du Pont de Nemours and Company ▲ HALAR is a registered trademark of Solvay Solexis