



Duty: Standard

Rolling Elements: Ball

Housing: Center Pull Take Up Frame & Take Up Housing

Self Alignment: +/- 2 Degrees


Lock: Setscrew

Optional Lock: SKWEZLOC Locking Collar

Seal: Felt

Optional Seal: Contact

Temperature: -20° to 220°F



STH Center Pull Take Up Frames

Bore Diameter		Part No.	Housing Assembly Included	Bearing Insert No.	Dimensions inch / mm														Bolt Size	Unit Wt. lb/kg	Frame Only Part No.
inch	mm				T Travel	A	B	C	D	E	F	G	J	K	N	R	S				
7/8		STH-14-6	ST-14	2-014	6 152.4	15 381.0	4 5/8 117.5	3 1/4 82.6	3/4 19.1	3 1/4 82.6	2 1/2 63.5	7 9/16 192.1	13/16 20.6	1 1/8 28.6	1 3/4 44.5	3/4 19.1	6 1/16 154.0	3/8	11.6 5.3	STH 12 TO 16-6 DZU	
		9 228.6			18 457.2	6 1/8 155.6	13.6 6.2												STH 12 TO 16-9 DZU		
		STH-14-9																			
15/16		STH-15-6	ST-15	2-015	6 152.4	15 381.0	4 5/8 117.5	3 1/4 82.6	3/4 19.1	3 1/4 82.6	2 1/2 63.5	7 9/16 192.1	13/16 20.6	1 1/8 28.6	1 3/4 44.5	3/4 19.1	6 1/16 154.0	3/8	11.6 5.3	STH 12 TO 16-6 DZU	
		9 228.6			18 457.2	6 1/8 155.6	13.6 6.2												STH 12 TO 16-9 DZU		
		STH-15-9																			
	25	STH-205-6	ST-205	5205	6 152.4	15 381.0	4 5/8 117.5	3 1/4 82.6	3/4 19.1	3 1/4 82.6	2 1/2 63.5	7 9/16 192.1	13/16 20.6	1 1/8 28.6	1 3/4 44.5	3/4 19.1	6 1/16 154.0	3/8	11.6 5.3	STH 12 TO 16-6 DZU	
		9 228.6			18 457.2	6 1/8 155.6	13.6 6.2												STH 12 TO 16-9 DZU		
		STH-205-9																			
1		STH-16-6	ST-16	2-1	6 152.4	15 381.0	4 5/8 117.5	3 1/4 82.6	3/4 19.1	3 1/4 82.6	2 1/2 63.5	7 9/16 192.1	13/16 20.6	1 1/8 28.6	1 3/4 44.5	3/4 19.1	6 1/16 154.0	3/8	11.6 5.3	STH 12 TO 16-6 DZU	
		9 228.6			18 457.2	6 1/8 155.6	13.6 6.2												STH 12 TO 16-9 DZU		
		STH-16-9																			
1 1/8		STH-18-6	ST-18	2-12	6 152.4	16 1/8 409.6	5 127.0	3 1/2 88.9	3/4 19.1	3 3/4 95.3	2 1/2 63.5	8 1/16 204.8	7/8 22.2	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	14.1 6.4	STH 17 TO 16-6 DZU	
		9 228.6			19 1/8 485.8	6 1/2 165.1	17.4 7.9												STH 17 TO 16-9 DZU		
		STH-18-9																			
	30	STH-206-6	ST-206	5206	6 152.4	16 1/8 409.6	5 127.0	3 1/2 88.9	3/4 19.1	3 3/4 95.3	2 1/2 63.5	8 1/16 204.8	7/8 22.2	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	14.1 6.4	STH 17 TO 19-6 DZU	
		9 228.6			19 1/8 485.8	6 1/2 165.1	16 7.3												STH 17 TO 19-9 DZU		
		STH-206-9																			
1 3/16		STH-19-6	ST-19	2-13	6 152.4	16 1/8 409.6	5 127.0	3 1/2 88.9	3/4 19.1	3 3/4 95.3	2 1/2 63.5	8 1/16 204.8	7/8 22.2	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	14.1 6.4	STH 17 TO 19-6 DZU	
		9 228.6			19 1/8 485.8	6 1/2 165.1	16 7.3												STH 17 TO 19-9 DZU		
		STH-19-9																			
1 1/4		STH-20-9	ST-20	2-14	9 228.6	19 11/16 500.1	6 13/16 173.0	3 7/8 98.4	3/4 19.1	4 101.6	2 1/2 63.5	8 1/16 204.8	1 25.4	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	16 7.3	STH 20 TO 23-9 DZU	
		12 304.8			22 11/16 576.3	8 5/16 211.1	19.5 8.8												STH 20 TO 23-12 DZU		
		STH-20-12																			
1 3/8		STH-22-9	ST-22	2-16	9 228.6	19 11/16 500.1	6 13/16 173.0	3 7/8 98.4	3/4 19.1	4 101.6	2 1/2 63.5	8 1/16 204.8	1 25.4	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	17.4 7.9	STH 20 TO 23-9 DZU	
		12 304.8			22 11/16 576.3	8 5/16 211.1	19.5 8.8												STH 20 TO 23-12 DZU		
		STH-22-12																			
	35	STH-207-9	ST-207	5207	9 228.6	19 11/16 500.1	6 13/16 173.0	3 7/8 98.4	3/4 19.1	4 101.6	2 1/2 63.5	8 1/16 204.8	1 25.4	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	17.4 7.9	STH 20 TO 23-9 DZU	
		12 304.8			22 11/16 576.3	8 5/16 211.1	19.5 8.8												STH 20 TO 23-12 DZU		
		STH-207-12																			
1 7/16		STH-23-9	ST-23	2-17	9 228.6	19 11/16 500.1	6 13/16 173.0	3 7/8 98.4	3/4 19.1	4 101.6	2 1/2 63.5	8 1/16 204.8	1 25.4	1 1/4 31.8	1 3/4 44.5	3/4 19.1	6 9/16 166.7	3/8	17.4 7.9	STH 20 TO 23-9 DZU	
		12 304.8			22 11/16 576.3	8 5/16 211.1	19.5 8.8												STH 20 TO 23-12 DZU		
		STH-23-12																			
1 1/2		STH-24-12	ST-24	2-18	12 304.8	23 9/16 598.5	8 9/16 217.5	4 1/4 108.0	7/8 22.2	4 1/4 108.0	2 1/2 63.5	9 5/16 236.5	1 3/16 30.2	1 3/8 34.9	2 50.8	7/8 22.2	7 9/16 192.1	3/8	27.2 12.3	STH 24 TO 28-12 DZU	
		18 457.2			29 9/16 750.9	11 9/16 293.7	32 14.5												STH 24 TO 28-18 DZU		
		STH-24-18																			

See notes on page G-78.