



SEALMASTER® PN Gold Mounted Ball Bearings

CRFS Bearings



Duty: Standard
Housing: High Strength Composite
 Two Bolt Flange
Self-Alignment: +/- 2 Degrees
Lock: Setscrew
Seal: HPS
Temperature: 0° to 150°F
Grease: Sealmaster GoldPlex-FG



CRFTC-PN Series 2 Bolt Flange Setscrew Locking Collar

Bore Diameter		Part No.	Bearing Insert No.	Basic Dynamic Rating lb/N	Dimensions inch/mm												Unit Wt. lb/kg	Open Cap	Closed Cap	Backside Shield	
					A	B	C	D	G	H	J	L	N	P	T	Bolt Size					
3/4	-	CRFTC-PN12	PN-12	2611	4 15/32	3 17/32	2 7/16	31/32	7/16	1 9/32	1 7/32	1 3/16	1/2	2 13/64	2	3/8	.70	ECO-12	ECC-12	2BSS-12	
-	20	CRFTC-PN204	PN-204	11614	113.5	89.7	61.9	24.6	11.1	32.5	31.0	30.2	12.7	56.0	50.8		.32			N/A	
1	-	CRFTC-PN16	PN-16	2801	4 15/16	3 57/64	2 23/32	1 5/64	17/32	1 7/16	1 3/8	1 3/8	9/16	2 23/64	2 3/16	7/16	.83	ECO-16	ECC-16	2BSS-16	
-	25	CRFTC-PN205	PN-205	12459	125.4	98.8	69.1	27.4	13.5	36.5	34.9	34.9	14.3	59.9	55.6		.38			N/A	
1 3/16	-	CRFTC-PN19	PN-19	4381 19488	5 11/16 144.5	4 19/32 116.7	3 1/4 82.6	1 7/32 31.0	17/32 13.5	1 9/16 39.7	1 1/2 38.1	1 19/32 40.5	5/8 15.9	2 31/64 63.1	2 9/16 65.1	7/16	2.45 1.11	ECO-19	ECC-19	2BSS-19	
1 1/4	-	CRFTC-PN20R	PN-20R															ECO-20R		2BSS-20R	
-	30	CRFTC-PN206	PN-206															ECO-19		2BSS-19	
1 1/4	-	CRFTC-PN20	PN-20	5782 25720	6 21/64 160.7	5 1/8 130.2	3 45/64 94.1	1 11/32 34.1	9/16 14.3	1 3/4 44.5	1 11/16 42.9	1 55/64 47.2	11/16 17.5	2 43/64 67.9	2 15/16 74.6	1/2	3.20 1.45	ECO-20	ECC-23	2BSS-20	
1 3/8	-	CRFTC-PN22	PN-22															ECO-23		2BSS-22	
1 7/16	-	CRFTC-PN23	PN-23																	2BSS-23	
-	35	CRFTC-PN207	PN-207																	2BSS-22	
1 1/2	-	CRFTC-PN24	PN-24	7340	6 29/32	5 21/32	4 7/64	1 1/2	9/16	2 1/64	1 15/16	2 1/16	3/4	2 15/16	3 19/64	1/2	2.45	ECO-24	ECC-24	2BSS-24	
-	40	CRFTC-PN208	PN-208	32650	175.4	143.7	104.4	38.1	14.3	51.2	49.2	52.4	19.1	74.6	83.7		1.11			2BSS-208	

Metric dimensions for reference only.

Not all parts are available from stock. Please contact customer service for availability (800) 626-2120.

For more information on bearing capabilities outside of our standard offering, please contact Application Engineering (800) 626-2093.