

SKM150GAL12T4



SEMITRANS® 2

Fast IGBT4 Modules

SKM150GAL12T4

Features


- IGBT4 = 4. generation fast trench IGBT (Infineon)
- CAL4 = Soft switching 4. generation CAL-diode
- Isolated copper baseplate using DBC technology (Direct Bonded Copper)
- Increased power cycling capability
- With integrated gate resistor
- For higher switching frequencies up to 20kHz
- UL recognized, file no. E63532

Typical Applications*

- Electronic welders at fsw up to 20 kHz
- DC/DC – converter
- Brake chopper
- Switched reluctance motor

Remarks

- Case temperature limited to $T_c = 125^\circ\text{C}$ max.
- Recommended $T_{op} = -40 \dots +150^\circ\text{C}$
- Product reliability results valid for $T_j = 150^\circ\text{C}$



GAL

Absolute Maximum Ratings

Symbol	Conditions		Values	Unit
IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 175 °C	T _c = 25 °C	232	A
		T _c = 80 °C	179	A
I _{Cnom}			150	A
I _{CRM}	I _{CRM} = 3xI _{Cnom}		450	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	μs
T _j			-40 ... 175	°C

Inverse diode

I_F	$T_j = 175^\circ\text{C}$	$T_c = 25^\circ\text{C}$	189	A
		$T_c = 80^\circ\text{C}$	141	A
I_{Fnom}			150	A
I_{FRM}	$I_{FRM} = 3 \times I_{Fnom}$		450	A
I_{FSM}	$t_p = 10\text{ ms, sin } 180^\circ, T_j = 25^\circ\text{C}$		900	A
T_j			-40 ... 175	$^\circ\text{C}$

Freewheeling diode

I_F	$T_j = 175^\circ\text{C}$	$T_c = 25^\circ\text{C}$	189	A
		$T_c = 80^\circ\text{C}$	141	A
I_{Fnom}			150	A
I_{FRM}	$I_{FRM} = 3 \times I_{Fnom}$		450	A
I_{FSM}	$t_p = 10\text{ ms, sin } 180^\circ, T_j = 25^\circ\text{C}$		900	A
T_j			-40 ... 175	$^\circ\text{C}$

Module

$I_{t(RMS)}$	$T_{terminal} = 80^\circ\text{C}$	200	A
T_{stg}		-40 ... 125	$^\circ\text{C}$
V_{isol}	AC sinus 50 Hz, $t = 1\text{ min}$	4000	V

Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
IGBT					
$V_{CE(sat)}$	$I_C = 150\text{ A}$ $V_{GE} = 15\text{ V}$ chipelevel	$T_j = 25^\circ\text{C}$	1.80	2.05	V
		$T_j = 150^\circ\text{C}$	2.20	2.40	V
V_{CE0}	chipelevel	$T_j = 25^\circ\text{C}$	0.8	0.9	V
		$T_j = 150^\circ\text{C}$	0.7	0.8	V
r_{CE}	$V_{GE} = 15\text{ V}$ chipelevel	$T_j = 25^\circ\text{C}$	6.67	7.67	$\text{m}\Omega$
		$T_j = 150^\circ\text{C}$	10.00	10.67	$\text{m}\Omega$
$V_{GE(th)}$	$V_{GE} = V_{CE}, I_C = 6\text{ mA}$	5	5.8	6.5	V
I_{CES}	$V_{GE} = 0\text{ V}$ $V_{CE} = 1200\text{ V}$	$T_j = 25^\circ\text{C}$		2.0	mA
		$T_j = 150^\circ\text{C}$			mA
C_{ies}	$V_{CE} = 25\text{ V}$ $V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$	9.3		nF
C_{oes}	$V_{CE} = 25\text{ V}$ $V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$	0.58		nF
C_{res}	$V_{CE} = 25\text{ V}$ $V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$	0.51		nF
Q_G	$V_{GE} = -8\text{ V} \dots +15\text{ V}$		850		nC
R_{Gint}	$T_j = 25^\circ\text{C}$		5.0		Ω



SEMITRANS® 2

Fast IGBT4 Modules

SKM150GAL12T4

Features

- IGBT4 = 4. generation fast trench IGBT (Infineon)
- CAL4 = Soft switching 4. generation CAL-diode
- Isolated copper baseplate using DBC technology (Direct Bonded Copper)
- Increased power cycling capability
- With integrated gate resistor
- For higher switching frequencies up to 20kHz
- UL recognized, file no. E63532


Typical Applications*

- Electronic welders at fsw up to 20 kHz
- DC/DC – converter
- Brake chopper
- Switched reluctance motor

Remarks

- Case temperature limited to $T_c = 125^\circ\text{C}$ max.
- Recommended $T_{op} = -40 \dots +150^\circ\text{C}$
- Product reliability results valid for $T_j = 150^\circ\text{C}$

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
t _{d(on)}	V _{CC} = 600 V	T _j = 150 °C		180		ns
t _r	I _C = 150 A	T _j = 150 °C		42		ns
E _{on}	V _{GE} = ±15 V	T _j = 150 °C		19.2		mJ
t _{d(off)}	R _{G on} = 1 Ω	T _j = 150 °C		410		ns
t _f	R _{G off} = 1 Ω	T _j = 150 °C		72		ns
E _{off}	di/dt _{on} = 3400 A/μs di/dt _{off} = 1750 A/μs	T _j = 150 °C		15.8		mJ
R _{th(j-c)}	per IGBT				0.19	K/W
Inverse diode						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		2.14	2.46	V
	V _{GE} = 0 V chipelevel	T _j = 150 °C		2.07	2.38	V
V _{F0}	chipelevel	T _j = 25 °C		1.3	1.5	V
		T _j = 150 °C		0.9	1.1	V
r _F	chipelevel	T _j = 25 °C		5.6	6.4	mΩ
		T _j = 150 °C		7.8	8.5	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		120		A
Q _{rr}	di/dt _{off} = 3100 A/μs	T _j = 150 °C		31.3		μC
E _{rr}	V _{GE} = ±15 V V _{CC} = 600 V	T _j = 150 °C		13		mJ
R _{th(j-c)}	per diode				0.31	K/W
Freewheeling diode						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		2.14	2.46	V
	V _{GE} = 0 V chipelevel	T _j = 150 °C		2.07	2.38	V
V _{F0}	chipelevel	T _j = 25 °C		1.3	1.5	V
		T _j = 150 °C		0.9	1.1	V
r _F	chipelevel	T _j = 25 °C		5.6	6.4	mΩ
		T _j = 150 °C		7.8	8.5	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		120		A
Q _{rr}	di/dt _{off} = 3100 A/μs	T _j = 150 °C		31.3		μC
E _{rr}	V _{GE} = ±15 V V _{CC} = 600 V	T _j = 150 °C		13		mJ
R _{th(j-c)}	per Diode				0.31	K/W
Module						
L _{CE}					30	nH
R _{CC'+EE'}	terminal-chip	T _C = 25 °C		0.65		mΩ
		T _C = 125 °C		1		mΩ
R _{th(c-s)}	per module			0.04	0.05	K/W
M _s	to heat sink M6		3		5	Nm
M _t		to terminals M5	2.5		5	Nm
						Nm
w					160	g



GAL




Fig. 1: Typ. output characteristic, inclusive $R_{CC'} + EE'$




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'}+EE'$




Fig. 11: CAL diode peak reverse recovery current






Fig. 12: Typ. CAL diode peak reverse recovery charge



SEMITRANS 2



GAL

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.