

LC1F150

TeSys F contactor - 3P(3 NO)-AC-3 $\leq$ 440V
150A with coil LX9 - 24...600V AC 40/400Hz, LX4
- 24...460V DC, LXE - 100...250V AC 50/60Hz or
100...380V DC

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys F
Product or component type	Contactor
Device short name	LC1F
Contactor application	Resistive load Motor control
Utilisation category	AC-1 AC-4 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	$\leq$ 690 V AC 50/60 Hz
[Ie] rated operational current	250 A 104 °F (40 °C) $\leq$ 440 V AC-1 150 A 131 °F (55 °C) $\leq$ 440 V AC-3
Motor power kW	75 kW at 380...400 V AC 50/60 Hz (AC-3) 80 kW at 415 V AC 50/60 Hz (AC-3) 80 kW at 440 V AC 50/60 Hz (AC-3) 90 kW at 500 V AC 50/60 Hz (AC-3) 40 kW 220...240 V AC 50/60 Hz AC-3) 100 kW at 660...690 V AC 50/60 Hz (AC-3) 22 kW at 400 V AC 50/60 Hz (AC-4)

Complementary

[Uc] control circuit voltage	24...575 V AC 40...400 Hz with LX1/LX9 coil 24...460 V DC with LX4 coil 100...250 V AC 50/60 Hz with LXE coil
------------------------------	---

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

100...380 V DC with LXE coil

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	250 A (at 40 °C)
Irms rated making capacity	1500 A IEC 60947-4-1
Rated breaking capacity	1200 A conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	1200 A 40 °C - 10 s 700 A 40 °C - 30 s 600 A 40 °C - 1 min 450 A 40 °C - 3 min 350 A 40 °C - 10 min
Associated fuse rating	160 A aM at ≤ 440 V 250 A gG at ≤ 440 V
Average impedance	0.35 mOhm - Ith 250 A 50 Hz
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	22 W AC-1 8 W AC-3
Control circuit voltage limits	Operational 0.85...1.1 Uc AC 40...400 Hz Drop-out 0.2...0.55 Uc AC 40...400 Hz Operational 0.85...1.1 Uc DC Drop-out 0.15...0.2 Uc DC Operational 85...275 V AC 50/60 Hz Drop-out 0...60 V AC 50/60 Hz Operational 85...418 V DC Drop-out 0...45 V DC
Heat dissipation	5.9...7.2 W 2.2...2.5 W
Operating time	35 ms closing with LX1/LX9 coil 130 ms opening with LX1/LX9 coil 30...40 ms closing with LX4 coil 30...50 ms opening with LX4 coil 40...80 ms closing with LXE coil 6...54 ms opening with LXE coil
Mounting support	Plate
Standards	IEC 60947-4-1 EN 60947-4-1 IEC 60947-1 EN 60947-1 JIS C8201-4-1
Product certifications	RINA CSA BV RMRoS LROS (Lloyds register of shipping) DNV ABS UL CB
Connections - terminals	Power circuit lugs-ring terminals 1 0.19 in ² (120 mm ²) 25 x 3 mm Power circuit: connector 1 cable(s) 120 mm ² Power circuit bar 2 Power circuit: bolted connection Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²)flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² solid without cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) Control circuit screw clamp terminals 1.0 0.00...0.00 in ² (0.25...2.5 mm ²)flexible without cable end Control circuit screw clamp terminals 1.0 0.00...0.00 in ² (0.25...2.5 mm ²)flexible with cable end Control circuit screw clamp terminals 1.0 0.00...0.00 in ² (0.2...2.5 mm ²)solid without cable end
Tightening torque	Power circuit: 18 N.m Control circuit 10.62 lbf.in (1.2 N.m) Control circuit 5.31 lbf.in (0.6 N.m)
Mechanical durability	10 Mcycles

Inrush power in VA	690...855 VA, 40...400 Hz cos phi 0.9 (at 68 °F (20 °C))with LX1/LX9 coil 543...665 VA (at 68 °F (20 °C))with LX4 coil 280...310 VA, 50/60 Hz cos phi 0.5 (at 68 °F (20 °C))with LXE coil 270...320 VA (at 68 °F (20 °C))with LXE coil
Hold-in power consumption in VA	6.6...8.1 VA 3.94...4.83 VA 4.5...7.0 VA 2.5...4.0 VA
Maximum operating rate	2400 cyc/h 131 °F (55 °C)
Compatibility code	LC1F

Environment

IP degree of protection	IP2x front face with shrouds IEC 60529 IP2x front face with shrouds conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-40...140 °F (-40...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	60...70 °C at Uc
Operating altitude	9842.52 ft (3000 m) without derating
Mechanical robustness	Vibrations contactor open2 Gn, 5...300 Hz Vibrations contactor closed: 6 Gn, 5...300 Hz Shocks contactor open9 Gn for 1/2 sine wave (11 ms) Shocks contactor closed15 Gn for 1/2 sine wave (11 ms)
Height	6.69 in (170 mm)
Width	6.44 in (163.5 mm)
Depth	6.73 in (171 mm)
Net Weight	8.44 lb(US) (3.83 kg)

Ordering and shipping details

Category	22336 - CTR,F-LINE,AC,OPEN,NONREV
Discount Schedule	I12
GTIN	00785901156116
Nbr. of units in pkg.	1
Package weight(Lbs)	8.1 lb(US) (3.67 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.17 in (18.2 cm)
Package 1 width	7.87 in (20 cm)
Package 1 Length	8.82 in (22.4 cm)
Package 2 Weight	7.91 lb(US) (3.588 kg)
Package 3 Weight	162.15 lb(US) (73.552 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------