

## Rigid Conduit/IMC Fittings

### Conduit Bushings — Die-Cast Zinc — Insulated

- 105° C thermoplastic liners
- Heavy reinforced ribs




| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |     | STD. CTN. |
|----------|--------------------|------------------|-----|-----------|
|          |                    | A                | B   |           |
| BU-801   | ½                  | 1.06             | .43 | 1,000     |
| BU-802   | ¾                  | 1.31             | .43 | 1,000     |
| BU-803   | 1                  | 1.59             | .48 | 500       |
| BU-804   | 1¼                 | 1.96             | .56 | 250       |
| BU-805   | 1½                 | 2.18             | .60 | 250       |

UL File No. E-23018.



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |     | STD. CTN. |
|----------|--------------------|------------------|-----|-----------|
|          |                    | A                | B   |           |
| BU-806   | 2                  | 2.68             | .56 | 250       |
| BU-807   | 2½                 | 3.25             | .90 | 50        |
| BU-808   | 3                  | 3.87             | .85 | 25        |
| BU-809   | 3½                 | 4.37             | .93 | 25        |
| BU-810   | 4                  | 5.00             | .93 | 10        |



### Conduit Bushings — Die-Cast Zinc — Heavy Reinforced Ribs




| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |          | STD. CTN. |
|----------|--------------------|------------------|----------|-----------|
|          |                    | A (MIN.)         | B (MAX.) |           |
| BU201    | ½                  | 1.05             | .37      | 1,000     |
| BU-202   | ¾                  | 1.32             | .37      | 1,000     |
| BU-203   | 1                  | 1.58             | .47      | 500       |
| BU-204   | 1¼                 | 1.94             | .50      | 250       |
| BU-205   | 1½                 | 2.20             | .52      | 250       |

UL File No. E-23018.



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |          | STD. CTN. |
|----------|--------------------|------------------|----------|-----------|
|          |                    | A (MIN.)         | B (MAX.) |           |
| BU-206   | 2                  | 2.69             | .52      | 250       |
| BU-207   | 2½                 | 3.23             | .85      | 50        |
| BU-208   | 3                  | 3.84             | .85      | 25        |
| BU-209   | 3½                 | 4.35             | .85      | 25        |
| BU-210   | 4                  | 5.02             | .85      | 10        |



### Insulated Bushings — Thermoplastic




| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.)                |                                 | STD. CTN. |
|----------|--------------------|---------------------------------|---------------------------------|-----------|
|          |                    | A                               | B                               |           |
| BU-501   | ½                  | 1 <sup>13</sup> / <sub>32</sub> | 1 <sup>1</sup> / <sub>16</sub>  | 400       |
| BU-502   | ¾                  | 1 <sup>13</sup> / <sub>32</sub> | 1 <sup>19</sup> / <sub>64</sub> | 400       |
| BU-503   | 1                  | 1 <sup>9</sup> / <sub>16</sub>  | 1 <sup>1</sup> / <sub>16</sub>  | 200       |
| BU-504   | 1¼                 | 1 <sup>9</sup> / <sub>16</sub>  | 1 <sup>29</sup> / <sub>32</sub> | 100       |
| BU-505   | 1½                 | 1 <sup>9</sup> / <sub>16</sub>  | 2 <sup>3</sup> / <sub>16</sub>  | 100       |
| BU-506   | 2                  | 1 <sup>5</sup> / <sub>8</sub>   | 2 <sup>11</sup> / <sub>16</sub> | 60        |

UL File No. E-23018 ½"-4" only.

Rated 105° C.



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.)                |                                 | STD. CTN. |
|----------|--------------------|---------------------------------|---------------------------------|-----------|
|          |                    | A                               | B                               |           |
| BU-507   | 2½                 | 2 <sup>23</sup> / <sub>32</sub> | 3 <sup>3</sup> / <sub>16</sub>  | 20        |
| BU-508   | 3                  | 2 <sup>9</sup> / <sub>16</sub>  | 3 <sup>27</sup> / <sub>32</sub> | 20        |
| BU-509   | 3½                 | 3 <sup>1</sup> / <sub>4</sub>   | 4 <sup>23</sup> / <sub>64</sub> | 5         |
| BU-510   | 4                  | 2 <sup>23</sup> / <sub>32</sub> | 4 <sup>27</sup> / <sub>32</sub> | 5         |
| BU-511   | 5                  | 1                               | 6 <sup>6</sup> / <sub>16</sub>  | 5         |
| BU-512   | 6                  | 1                               | 7 <sup>1</sup> / <sub>16</sub>  | 5         |



### Bushings — Iron/Zinc Plated




| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.)                |                                | STD. CTN. |
|----------|--------------------|---------------------------------|--------------------------------|-----------|
|          |                    | A                               | B                              |           |
| BU-401   | ½                  | 1 <sup>1</sup> / <sub>32</sub>  | 7 <sup>1</sup> / <sub>16</sub> | 1,000     |
| BU-402   | ¾                  | 1¼                              | 7 <sup>1</sup> / <sub>16</sub> | 1,000     |
| BU-403   | 1                  | 1 <sup>1</sup> / <sub>16</sub>  | ½                              | 500       |
| BU-404   | 1¼                 | 1 <sup>15</sup> / <sub>16</sub> | 1 <sup>1</sup> / <sub>32</sub> | 200       |
| BU-405   | 1½                 | 2 <sup>13</sup> / <sub>64</sub> | 9 <sup>1</sup> / <sub>16</sub> | 100       |
| BU-406   | 2                  | 2 <sup>5</sup> / <sub>64</sub>  | 9 <sup>1</sup> / <sub>16</sub> | 50        |

UL File No. E-23018.



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.)                |                                | STD. CTN. |
|----------|--------------------|---------------------------------|--------------------------------|-----------|
|          |                    | A                               | B                              |           |
| BU-401   | ½                  | 1 <sup>1</sup> / <sub>32</sub>  | 7 <sup>1</sup> / <sub>16</sub> | 1,000     |
| BU-402   | ¾                  | 1¼                              | 7 <sup>1</sup> / <sub>16</sub> | 1,000     |
| BU-403   | 1                  | 1 <sup>1</sup> / <sub>16</sub>  | ½                              | 500       |
| BU-404   | 1¼                 | 1 <sup>15</sup> / <sub>16</sub> | 1 <sup>1</sup> / <sub>32</sub> | 200       |
| BU-405   | 1½                 | 2 <sup>13</sup> / <sub>64</sub> | 9 <sup>1</sup> / <sub>16</sub> | 100       |
| BU-406   | 2                  | 2 <sup>5</sup> / <sub>64</sub>  | 9 <sup>1</sup> / <sub>16</sub> | 50        |



### Grounding Bushings — Die-Cast Zinc — Insulated with Aluminum Lay-in Type Lug

- 105° C thermoplastic liners
- Heavy reinforced ribs



| CAT. NO. | TRADE SIZE (IN.) | GROUNDING LUG WIRE SIZE |         | STD. CTN. |
|----------|------------------|-------------------------|---------|-----------|
|          |                  | MIN.                    | MAX.    |           |
| BG201    | ½                | 14 AWG                  | 4 AWG   | 500       |
| BG-202   | ¾                | 14 AWG                  | 4 AWG   | 500       |
| BG-203   | 1                | 14 AWG                  | 4 AWG   | 250       |
| BG-204A  | 1¼               | 14 AWG                  | 4 AWG   | 200       |
| BG-204   | 1¼               | 8 AWG                   | 1/0 AWG | 200       |
| BG-205A  | 1½               | 11 AWG                  | 4 AWG   | 100       |
| BG-205   | 1½               | 8 AWG                   | 1/0 AWG | 50        |
| BG-206A  | 1                | 14 AWG                  | 4 AWG   | 100       |
| BG-206   | 2                | 8 AWG                   | 1/0 AWG | 50        |

UL File No. E-3060.



| CAT. NO. | TRADE SIZE (IN.) | GROUNDING LUG WIRE SIZE |           | STD. CTN. |
|----------|------------------|-------------------------|-----------|-----------|
|          |                  | MIN.                    | MAX.      |           |
| BG-207   | 2½               | 8 AWG                   | 1/0 AWG   | 50        |
| BG-207A  | 2½               | 6 AWG                   | 250 kcmil | 50        |
| BG-208   | 3                | 8 AWG                   | 1/0 AWG   | 50        |
| BG-208A  | 3                | 6 AWG                   | 250 kcmil | 50        |
| BG-209   | 3½               | 8 AWG                   | 1/0 AWG   | 10        |
| BG-209A  | 3½               | 6 AWG                   | 250 kcmil | 10        |
| BG-210   | 4                | 8 AWG                   | 1/0 AWG   | 10        |
| BG-210A  | 4                | 6 AWG                   | 250 kcmil | 10        |

