







Technical data and measuring conditions.

Rated Voltage V_R	530/310 V AC, 50/60Hz.				
Rated Current I_R	Referred to 40 °C ambient temperature				
Test Voltage V_{test}	2280 V DC, 2 s (line/line) 2690 V DC, 2 s (line/case)				
Overload Capability (thermal)	1.5 · I_R for 3 min per hour or 2.5 · I_R for 30 s per hour				
Leakage Current I_{leak}	At 530 V AC, 50 Hz.				
Climatic Category (IEC 60068-1)	25/100/21 (-25 °C/+100 °C/21 days damp heat test)				
Approvals	UL 1283, CSA C22.2 No. 8, 500/290V				

V_R	I_R	I_{leak}	$R_{typ.}$	Approx. Weight
AC				kg. / lbs.
V	A	mA	μ ohm	
530/310	2500	< 20	15	105 / 231

				TOLERANCES (EXCEPT AS NOTED)	 7878 N. 86th STREET MILWAUKEE, WI 53224
				DECIMAL	
				.XX ±.02	KRF FILTER KRF2500ACB, 200-480V, 2500A
				.XXX ±.01	
				FRACTIONAL	DRN. BY DSW DATE 1/06/2010 DWG. NO. CKRF2500ACB
				± 1/32	
				ANGULAR	SCALE TO FIT
				± 1/2°	APPRVD.
NO	REVISION	DATE	BY		SHT. 1 OF 1