

TECO Westinghouse

ISSUED February 8, 2013	PERFORMANCE DATA 3-PHASE INDUCTION MOTOR	ENCLOSURE WP1
TYPE AMRCHN		CATALOG# VHP4004

NAMEPLATE INFORMATION

OUTPUT		POLE	FRAME SIZE	VOLTAGE	HZ	RATED AMBIENT	INS. CLASS	NEMA DESIGN	TIME RATING	SERVICE FACTOR
HP	KW									
400	298.4	4	449TP	230/460	60	40°C	F	B	CONT.	1.15

TYPICAL PERFORMANCE

FULL LOAD RPM	EFFICIENCY				POWER FACTOR			MAXIMUM POWER FACTOR CORRECTION
	FULL LOAD		3/4 LOAD %	1/2 LOAD	F. L. %	3/4 LOAD	1/2 LOAD %	
	MIN. %	NOM. %						
1787	95.0	95.8	95.4	94.5	88.5	85.0	82.0	101.6 KVAR

CURRENTS

NO LOAD				FULL LOAD			LOCKED ROTOR			NEMA KVA CODE LETTER
	AT 230 VOLT		AT 460 VOLT		AT 230 VOLT	AT 460 VOLT		AT 230 VOLT	AT 460 VOLT	
	-		127.50		884.0	442.0		-	2960.0	

TORQUE

INERTIA

ACCEL TIME

FULL LOAD lb-ft	LOCKED ROTOR %FLT	PULL UP %FLT	BREAK DOWN %FLT	ROTOR WR ² lb-ft ²	NEMA LOAD WK ² lb-ft ²	MAX ALLOWABLE WK ² lb-ft ²	NEMA LOAD WK ² Sec	MAX ALLOWABLE WK ² Sec
1179.00	125	105	205	92.00	1546	2319	5.01	7.38

SAFE STALL
TIME IN
SECONDS

ALLOWABLE
STARTS
PER HOUR

SOUND
PRESSURE
LEVEL @ 3 FT
dB(A)

DOWNTHRUST
L10:8800 HOURS

COLD

HOT

COLD

HOT

20

15

2

1

79.0

13200

APPROVED:

M. PRATER

DRAWING NO.

31057VHP4004

REVISION **0**