


Three Phase Bridge, 130/160 A (Power Modules)



MTK

FEATURES

- Package fully compatible with the industry standard INT-A-PAK power modules series
- High thermal conductivity package, electrically insulated case
- Excellent power volume ratio
- 4000 V_{RMS} isolating voltage
- UL E78996 approved 
- Totally lead (Pb)-free
- Designed and qualified for industrial level



RoHS
COMPLIANT

PRODUCT SUMMARY

I _O	130/160 A
----------------	-----------

DESCRIPTION

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and heavy duty applications.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	130MT.K	160MT.K	UNITS
I _O		130 (160)	160 (200)	A
	T _C	85 (62)	85 (60)	°C
I _{FSM}	50 Hz	1130	1430	A
	60 Hz	1180	1500	
I ² _t	50 Hz	6400	10 200	A ² s
	60 Hz	5800	9300	
I ² _{√t}		64 000	102 000	A ² √s
V _{RRM}	Range	800 to 1600		V
T _{Stg}	Range	- 40 to 150		°C
T _J				

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V _{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V _{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I _{RRM} MAXIMUM AT T _J = MAXIMUM mA
130-160MT..K	80	800	900	10
	100	1000	1100	
	120	1200	1300	
	140	1400	1500	
	160	1600	1700	

130-160MT..KPbF Series



Vishay High Power Products Three Phase Bridge, 130/160 A (Power Modules)

FORWARD CONDUCTION							
PARAMETER	SYMBOL	TEST CONDITIONS			130MT.K	160MT.K	UNITS
Maximum DC output current at case temperature	I _O	120° rect. conduction angle			130 (160)	160 (200)	A
					85 (62)	85 (60)	°C
Maximum peak, one-cycle forward, non-repetitive surge current	I _{TSM}	t = 10 ms	No voltage reapplied	Initial T _J = T _J maximum	1130	1430	A
		t = 8.3 ms					
		t = 10 ms	100 % V _{RRM} reapplied		950	1200	
		t = 8.3 ms			1000	1260	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		64 000	102 000	A ² s
		t = 8.3 ms					
		t = 10 ms	100 % V _{RRM} reapplied		4500	7200	
		t = 8.3 ms			4100	6600	
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reapplied			64 000	102 000	A ² √s
Low level value of threshold voltage	V _{T(TO)1}	(16.7 % x π x I _{T(AV)}) < I < π x I _{T(AV)}), T _J maximum			0.78	0.81	V
High level value of threshold voltage	V _{T(TO)2}	(I > π x I _{T(AV)}), T _J maximum			0.99	1.04	
Low level value of forward slope resistance	r _{f1}	16.7 % x π x I _{T(AV)}) < I < π x I _{T(AV)}), T _J maximum			4.59	3.52	mΩ
High level of forward slope resistance	r _{f2}	(I > π x I _{T(AV)}), T _J maximum			4.17	3.13	
Maximum forward voltage drop	V _{FM}	I _{pk} = 200 A, T _J = 25 °C, t _p = 400 μs single junction			1.63	1.49	V
RMS isolation voltage	V _{ISOL}	T _J = 25 °C, all terminal shorted f = 50 Hz, t = 1 s			4000		

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS	130MT.K	160MT.K	UNITS
Maximum junction operating and storage temperature range	T _J , T _{Stg}		- 40 to 150		°C
Maximum thermal resistance, junction to case	R _{thJC}	DC operation per module	0.16	0.12	K/W
		DC operation per junction	0.93	0.73	
		120° rect. conduction angle per module	0.18	0.15	
		120° rect. conduction angle per junction	1.08	0.88	
Maximum thermal resistance, case to heatsink	R _{thCS}	Per module Mounting surface smooth, flat and greased	0.03		
Mounting torque ± 10 %	to heatsink to terminal	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound.	4 to 6		Nm
			3 to 4		
Approximate weight		Lubricated threads.	176		g




Fig. 1 - Current Ratings Characteristic




Fig. 2 - Forward Voltage Drop Characteristics





Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current




Fig. 5 - Maximum Non-Repetitive Surge Current

130-160MT..KPbF Series

Vishay High Power Products Three Phase Bridge, 130/160 A
(Power Modules)




Fig. 6 - Current Ratings Characteristic




Fig. 7 - Forward Voltage Drop Characteristics





Fig. 8 - Total Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current




Fig. 10 - Maximum Non-Repetitive Surge Current




Fig. 11 - Thermal Impedance Z_{thJC} Characteristics


ORDERING INFORMATION TABLE

Device code	16	0	MT	160	K	PbF
	①	②	③	④	⑤	
1	- Current rating code: 13 = 130 A (average) 16 = 160 A (average)					
2	- Three phase diodes bridge					
3	- Essential part number					
4	- Voltage code x 10 = V_{RRM} (see Voltage Ratings table)					
5	- PbF = Lead (Pb)-free					

Note

- To order the optional hardware go to www.vishay.com/doc?95172

CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS	
Dimensions	http://www.vishay.com/doc?95004



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.