




W1G208 Series

Tubeaxial

Ø 232x80mm


- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics.
- Maintenance-free ball bearings.
- Die-cast aluminum housing, GDALSi. Impeller of plastic PA6.6, black.
- Mounting from either face using four 4.5 mm holes.
- Air exhaust over struts. Rotational direction CCW looking at rotor.
- Standard terminal strip, cable exit possible via terminal strip.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VDC	Volt. Range	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
W1G208-BA35-52	1	618.0	24	16 to 28	96	74	72	Ball	Terminal	5.07
W1G208-BA73-52	1	618.0	48	36 to 57	96	74	72	Ball	Terminal	5.07



	N [RPM]	P ₁ [W]	η ₀ [%]	L _{pA} [dBA]
1 ①	3740	116	—	75
1 ②	3500	118	52	74
1 ③	3450	119	53	73
1 ④	3530	118	48	75
1 ①	3500	96	—	74
1 ②	3300	99	52	72
1 ③	3250	100	53	72
1 ④	3330	99	48	73
1 ⑤	2960	58	—	70
1 ⑥	2830	63	52	69
1 ⑦	2780	64	53	68
1 ⑧	2840	62	48	70

Curve



ebmpapst

e-mail: sales@us.ebmpapst.com · TEL: 860-674-1515 · FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2006 © ebm-papst Inc. reserves the right to change any specifications or data without notice