



Nominal data

Type	7114 NH	
Nominal voltage	VDC	24
Nominal voltage range	VDC	12 .. 26.5
Speed (rpm)	min ⁻¹	3350
Power consumption	W	19.0
Min. ambient temperature	°C	-25
Max. ambient temperature	°C	72
Air flow	m ³ /h	360
Sound power level	B	6.7
Sound pressure level	dB(A)	58

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment
Subject to change

Technical description

General description	* Power consumption when wide open; these values may be considerably higher at the operating point.
Weight	0.620 kg
Dimensions	Ø 150 x 38 mm
Impeller material	Sheet steel, painted black
Housing material	Die-cast aluminum
Airflow direction	Exhaust over struts
Direction of rotation	Counterclockwise, viewed toward rotor
Storage	Ball bearing
Service life L10 at 40 °C	75000 h
Service life L10 at maximum temperature	35000 h
Cable	Leads AWG 22, TR 64, stripped and tin-plated.
Motor protection	Protection against reverse polarity and blocked rotor.
Locked-rotor protection	Electronic locked-rotor protection
Approval	VDE, CSA, UL, CE

Technical drawing of a fan assembly. The drawing shows a fan with a circular frame and a central hub. The fan is mounted on a rectangular plate. The dimensions are as follows:

- Overall width: $38^{+0.5}$
- Overall height: 365^{+10}
- Mounting plate thickness: 6 ± 1
- Mounting plate width: 6
- Mounting plate height: $4.3^{+0.15}$
- Mounting plate diameter: $\varnothing 150^{+0.5}$
- Mounting plate hole diameter: $\varnothing 146$
- Mounting plate hole position: $4.5^{+0.2}$
- Mounting plate hole diameter: $\varnothing 162^{+0.2}$

Curves: Air performance

